


MODBUS Management Accessory Card for UPS Remote Monitoring and Control

MODEL NUMBER: MODBUSCARD



Highlights

- Internal MODBUS management accessory card
- Simple installation and setup
- Implements MODBUS RTU protocol
- Provides RS-422/485 and RS-232 interfaces

Package Includes

- MODBUSCARD
- Installation Guide

Description

MODBUSCARD provides UPS systems with the functionality of communication with PCs via MODBUS. Implements MODBUS RTU protocol. Provides MODBUS functions including Read Coils, Discrete Inputs, Holding Registers, Input Registers, Write Single Coil and Single Register. Provides RS-422/485 and RS-232 interfaces (PC communicates with UPS via RS-422/485 or RS-232 or both at the same time). Three sets of eight dip switches support Card ID, RS-232 and RS-422/485 configurations. Includes RS-422/485 and RS-232 communications ports. See manual for detailed setup instructions and full set of functions and configuration options. Compatible with select SmartOnline® UPS models only (MODBUSCARD should be listed within the "UPS Accessories" or "Power Management & Hardware" sections of the compatible UPS product webpage).

Features

- MODBUSCARD provides UPS systems with the functionality of communication with PCs via MODBUS.
- Implements MODBUS RTU protocol.
- Provides MODBUS functions including Read Coils, Discrete Inputs, Holding Registers, Input Registers, Write Single Coil and Single Register.
- Provides RS-422/485 and RS-232 interfaces (PC communicates with UPS via RS-422/485 or RS-232 or both at the same time).
- Three sets of 8 dipswitches support Card ID, RS-232 and RS-422/485 configurations. Includes RS-422/485 and RS-232 communications ports. See manual for detailed setup instructions and full set of functions and configuration options.
- Compatible with select SmartOnline UPS models only (The MODBUSCARD should be listed within the "UPS Accessories" or "Power Management & Hardware" sections of the compatible UPS product webpage).

Specifications

OVERVIEW	
UPC Code	037332157065
PHYSICAL	



Powering Business Worldwide



Shipping Dimensions (hwd / in.)	1.60 x 6.00 x 6.00
Shipping Dimensions (hwd / cm)	4.06 x 15.24 x 15.24
Shipping Weight (lbs.)	0.55
Shipping Weight (kg)	0.25
Unit Dimensions (hwd / in.)	0.600 x 2.350 x 5.280
Unit Dimensions (hwd / cm)	1.5 x 6.1 x 13.5
Unit Weight (lbs.)	0.11
Unit Weight (kg)	0.05
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.