


Safe-IT 2-Port Antibacterial Wall-Mount Insert, Decora Style, Vertical, Ivory, TAA

MODEL NUMBER: N042DAB-002V-IV



Decora-style insert combines with compatible wall-mount faceplate for terminating premise audio/video, voice or data cable applications.

Features

Decora-Style Insert Connects Audio/Video, Voice and Data Cable Lines at the Wall

This vertical-style center insert combines with a Tripp Lite or other compatible Decora-style wall plate (sold separately) to complete an in-wall wiring application, such as home theater (audio/video), VoIP phones (voice) and Ethernet (data). Any type of keystone jack, including those used in HDMI, DisplayPort, RCA, USB and Cat5e/6/6a installations, snaps easily into the cutouts for quick cable connection.

Provides Extra Protection Against Certain Bacteria

The N042DAB-002V-IV is constructed using an antibacterial material that is effective in inhibiting Escherichia coli (E. coli) and Staphylococcus aureus (staph) and tested to ISO 22196:2011 standards. This added protection makes this cover plate an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This durable ivory-colored insert blends elegantly into any home or office décor for a sleek, professional installation. Mounting screws are included. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

TAA-Compliant for GSA Schedule Purchases

The N042DAB-002V-IV is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332269034
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB 2.0 (High Speed)
Country/Region	Global

Highlights

- Ideal for home theater, VoIP or Ethernet premise wiring installations
- Made with antibacterial material proven effective in inhibiting E. coli and staph
- Compatible with any type of keystone jack, including HDMI, Cat5/6, USB and DisplayPort
- High-impact plastic construction designed to blend in with your home/office décor
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- N042DAB-002V-IV 2-Port Antibacterial Wall-Mount Insert, Ivory
- (2) Mounting screws



PHYSICAL	
Color	Ivory
Material of Construction	Faceplate: ABS; Copper Pillars: Brass
Total Number of Ports	2
Unit Dimensions (hwd / in.)	4.154 x 1.319 x 0.437
Finish	Gloss
ENVIRONMENTAL	
Operating Temperature Range	14 TO 140 F (-10 to 60 C)
Storage Temperature Range	-40 TO 154.4 F (-40 to 68 C)
Operating Humidity Range	10% TO 90% RH, (NON-CONDENSING)
Storage Humidity Range	10% TO 90% RH, (NON-CONDENSING)
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	(2) KEYSTONE JACK CUTOUT
FEATURES & SPECIFICATIONS	
Antibacterial	Yes
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>