



Powering Business Worldwide

Solid PVC Cable

MODEL NUMBER: **N022-250-GY**

Description

Tripp Lite's 250-ft. gray category 5e (Cat5e) solid PVC bulk cable is designed for premise (in-wall) cabling applications. This 24 AWG 4-pair solid cable has a PVC jacket and is rated for 350MHz/1Gbps communication. Used for all non-plenum horizontal wiring applications. Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC11801 and ETL (category 5e draft 11). Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Designed for premise (in-wall) cabling applications
- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 250-ft. Color: gray
- 24 AWG 4-pair solid cable with PVC jacket
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other lengths
- Available in stranded copper cable (N020-01K-GY), in plenum cable (N024-01K) and in Cat6 (N222-01K and N224-01K)
- Warranted to be free from defects in materials and workmanship for life

Highlights

- Premium cabling for Category 5 and 5e applications — rated for 350 MHz/1Gbps communications

System Requirements

- For all non-Plenum horizontal premise (in-wall) wiring applications for Network Installations 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications.

Package Includes

- 250-ft. Cat5e Gray Bulk Patch Cable Solid PVC 24AWG 350MHz

Specifications

OVERVIEW	
UPC Code	037332013095
Technology	Cat5/5e
PHYSICAL	
Color	Gray
Cable Shielding	UTP
Cable Length (ft.)	250
Cable Length (m)	76.22
Shipping Dimensions (hwd / in.)	0.00 x 0.00 x 0.00
Shipping Weight (lbs.)	6.94
Shipping Weight (kg)	3.15
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.