

Single-Gang Surface-Mount Back Box, White, TAA

MODEL NUMBER: **N080-SMB1-WH**



Deep back box for mounting a wallplate as part of a raceway system. Ideal for multiple audio/video, voice and Ethernet in-wall applications using any type of keystone jack, including Cat5e/6/6a, USB, HDMI, DisplayPort and RCA.

Description

The N080-SMB1-WH Single-Gang Surface-Mount Junction Box is perfect for mounting a wallplate to complete multiple audio/video, voice and Ethernet in-wall connections using any type of keystone jack, including Cat5e/6/6a, USB, HDMI, DisplayPort and RCA. Designed to work with mid-sized and standard single-gang wallplates, such as Tripp Lite's N080-Series, this back box is two inches deep. It features raceway cutouts in three different sizes (1 inch, 1.25 inches and 1.75 inches in diameter) on each side, as well as a rectangular knockout on the back. The cover snaps securely to the base with no screws required. Made from durable ABS thermoplastic. White color blends elegantly into any home or office décor for a sleek, professional installation. Includes two mounting screws for easy installation. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

Completes Multiple A/V, Voice and Ethernet In-Wall Applications

- Compatible with mid-sized and standard single-gang wallplates (including Tripp Lite's N080-Series)
- 2 in. deep
- Raceway cutouts on each side in 3 sizes: 1, 1.25 and 1.75 in. diameter
- Rear rectangular knockout
- Mounting hardware included

Durable Construction

- Made from high-impact ABS thermoplastic
- Comes in white to blend into home or office décor

Highlights

- Accepts mid-sized and standard wallplates
- Raceway cutouts in 3 sizes: 1, 1.25 and 1.75 in. diameter
- White color blends into any home or office décor
- Durable ABS thermoplastic construction
- Includes mounting screws

Package Includes

- N080-SMB1-WH Single-Gang Surface-Mount Junction Box, White
- Mounting hardware



- Cover snaps to the base with no screws required

TAA Compliant

- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332195586
Technology	Cat5/5e; Cat6; Cat6a; USB 2.0 (High Speed); USB 3.0 (SuperSpeed); HDBaseT; HDMI; USB; DisplayPort
PHYSICAL	
Color	White
Shipping Dimensions (hwd / cm)	1.27 x 17.98 x 27.00
Shipping Dimensions (hwd / in.)	0.50 x 7.08 x 10.63
Shipping Weight (kg)	0.13
Shipping Weight (lbs.)	0.28
Unit Dimensions (hwd / cm)	128 x 8 x 5
Unit Dimensions (hwd / in.)	5.10 x 3.30 x 2.10
Unit Weight (kg)	0.12
Unit Weight (lbs.)	0.27
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 - 60 C)
Storage Temperature Range	-40 to 154.4 F (-40 to 68 C)
Operating Humidity Range	10 to 90% RH
CONNECTIONS	
Side A - Connector 1	KEYSTONE JACK CUTOUT
Side B - Connector 1	KEYSTONE JACK CUTOUT
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>