

Cat3 25-Pair Telco Cable (RJ21 M to Open End), 50-ft.

MODEL NUMBER: **N154-050-C3**



Highlights

- 50ft, 26AWG Cat3 UTP copper cable for extending voice connections
- Male to Open End for punch down blocks
- Use with Telephone, PBX, IP Phone Systems

System Requirements

- Communication equipment and connectivity devices utilizing 50pin Telco type connections and 66M punch down blocks

Package Includes

- 1 - 50ft Cat3 25-Pair Telco Cable, RJ21 Male to Open End

Description

Tripp Lite's N154 series Telco cables are ideal for telephone, PBX, and IP Phone system applications. Constructed with 26AWG, solid conductor, Cat3 rated cable, heavy duty metal backshells with Male RJ21, 50 pin connectors, to Open End for punching down to 66M blocks. EIA/TIA 568B color coded conductors. N154 cables are available in stock lengths of 25ft, 50ft, and 100ft (N154-025-C3, N154-050-C3, N154-100-C3).

Features

- 50ft, 26AWG Cat3 UTP copper cable for extending voice connections
- Male 50pin Centronics Telco connector to Open End
- Use with Telephone, PBX, and IP Phone Systems
- EIA/TIA 568B color code
- PVC Jacket
- Rugged metal backshell connectors
- RoHS Compliant

Specifications

OVERVIEW	
UPC Code	037332153449
Technology	Cat3
CONNECTIONS	
Side A - Connector 1	CENTRONICS 50 (MALE)
Side B - Connector 1	CENTRONICS 50 (FEMALE)

PHYSICAL	
Color	Gray
Cable Shielding	UTP
Wire Type	Solid
Cable Length (ft.)	50
Cable Length (m)	15.24
Cable Length (in.)	600
Cable Length (cm)	1524
Shipping Dimensions (hwd / in.)	14.20 x 11.00 x 0.50
Shipping Dimensions (hwd / cm)	36.07 x 27.94 x 1.27
Shipping Weight (lbs.)	3.50
Shipping Weight (kg)	1.59
FEATURES & SPECIFICATIONS	
Snagless Connector	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Product Warranty Period (International)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.