


## 2-Port Single Gang Faceplate, Stainless Steel, Industrial Grade, IP44, TAA

MODEL NUMBER: N206-FP02-IND



Bulkhead wall plate combines with a coupler and industrial Cat5e/6, USB 3.0 or 4K HDMI cable to complete an IP44 connection.

### Features

**Bulkhead Wall Plate Recommended for Outdoor or Harsh Indoor Environments** This single-gang industrial bulkhead face plate is ideal for connecting Cat5e/6 networks, USB 3.0 or 4K HDMI installations in outdoor applications and other areas where protection from harsh elements is essential. The stainless steel frame and rubber back gasket contribute to the wall plate's IP44 rating, which ensures protection from splashing water from all directions. Wall-mounting hardware is included.

**Designed for Use with Tripp Lite Industrial-Grade Cables and Couplers** The bulkhead wall plate with two cutouts is recommended for use with Tripp Lite's N206-Series industrial Cat5e/6 patch cables and N206-BC01-IND bulkhead coupler or N206-KJ01-IND keystone jack, the U325-Series industrial USB 3.0 cables and U325-000-IND bulkhead coupler and the P569-000-FF-IND bulkhead coupler and P569-Series industrial 4K HDMI cables (all sold separately).

**TAA-Compliant for GSA Schedule Purchases** The N206-FP02-IND is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

**Lifetime Warranty** The N206-FP02-IND is backed by a lifetime warranty, ensuring reliability and performance.

### Highlights

- Built to protect Gigabit Ethernet and digital signage applications in harsh environments
- IP44-rated to prevent splashing water from damaging cables and other equipment
- Designed for Tripp Lite industrial cables and couplers—no guessing about compatibility
- Wall-mounting hardware included for immediate installation
- Complies with Federal Trade Agreements Act standards for GSA Schedule purchases

### Applications

- Connect Gigabit Ethernet networks, security cameras or digital signage in factories, warehouses, recycling plants, machine shops and other industrial environments
- Provide Cat6, USB 3.0 or 4K HDMI connectivity in outdoor environments susceptible to rain, such as a stadium or outdoor arena
- Set up outdoor digital signage at malls, theaters and bus stops

### Package Includes

- N206-FP02-IND Bulkhead Wall Plate, 2 Cutouts, Industrial, Metal
- (2) Wall-mounting screws
- (2) Washers
- Quick Start Guide



## Specifications

OVERVIEW	
UPC Code	037332206268
Technology	Cat5/5e; Cat6; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
PHYSICAL	
Color	Silver
Included Mounting Accessories	SCREW (X2), SCREW WASHER (X2)
Shipping Dimensions (hwd / cm)	19.56 x 12.70 x 1.27
Shipping Dimensions (hwd / in.)	7.70 x 5.00 x 0.50
Shipping Weight (kg)	0.08
Shipping Weight (lbs.)	0.17
SPECIAL FEATURES	
Snagless Connector	No
STANDARDS & COMPLIANCE	
Certifications	Tested to RoHS, REACH, UL, IP44
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>