

Cat6 RJ45 Pass-Through UTP Modular Plug, 50 Pack

MODEL NUMBER: N232-050-UTP



Clear RJ45 Cat6 connectors terminate round solid or stranded conductor cabling in data and voice Ethernet applications.

Features

50 Pack of RJ45 Modular Plugs for Terminating Solid or Stranded Cat6 Cable

These RJ45 modular connectors make it easy to terminate solid or stranded conductor Cat6 cable in your data or voice Ethernet application. The RJ45 pass-through UTP (Unshielded Twisted Pair) plugs work with most RJ45 crimping tools (except AMP) and custom-length 24–26 AWG UTP Cat6 cable. Conveniently packed in a rugged plastic bag that fits perfectly in your toolbox, these durable clear connectors feature 50-micron gold-plated contacts for optimal signal transmission and staggered nose patterns for minimal near-end crosstalk (NEXT).

Highlights

- 50 Cat6 RJ45 pass-through UTP modular plugs in an easy-to-pack plastic bag
- Work with most RJ45 crimping tools and 24–26 AWG UTP Cat6 cables
- 50 m gold-plated contacts promote premium data transfer
- Staggered nose pattern reduces near-end crosstalk for clearer transmission
- Ideal for use with solid or stranded conductor Cat6 cable in your Ethernet application

Applications

Terminate solid or stranded conductor cabling in Cat6 network applications

Package Includes

(50) Cat6 RJ45 pass-through UTP modular plugs

Specifications

| OVERVIEW | |
|-----------------------------|------------------------------|
| UPC Code | 037332260697 |
| Technology | Cat6; Cat6a |
| PHYSICAL | |
| Cable Shielding | UTP |
| Wire Gauge (AWG) | 24 - 26 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -40 to 185 °F (-40 to 85 °C) |
| Storage Temperature Range | 41 to 86 °F (5 to 30 °C) |
| Relative Humidity | 15 to 65% RH, Non-Condensing |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| WARRANTY | |
|-------------------------------------|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>