

## Keystone Jack Cat6/Cat5e, RJ45, Shuttered, Dust Cap - Toolless, PoE/PoE+ Compliant, White, TAA

MODEL NUMBER: N238-001-GY-TF



Toolless RJ45 keystone jack lets you terminate your Cat6/5e network patch cable without using a punchdown tool.

### Features

**Toolless Keystone Jack Strengthens Your High-Speed Cat5e/Cat6 Network** Terminate your network patch cable without the time, effort and expense of a punchdown tool. Ideal for Cat6 premise wiring, the RJ45 keystone jack snaps into wall plates, patch panels and surface-mount boxes and works with all shielded Cat6 cables. Toolless punchdown connection is compatible with 22–24 AWG solid wire cabling. A shutter/dust cap protects the jack from dust and other contaminants when not in use.

**Specifically Designed for Use in Surveillance, VoIP and Other PoE+ Applications** This PoE+ (Power over Ethernet) jack prevents spark-gap erosion that degrades the plug and jack contacts over time and can affect data and/or power transmission capabilities to maximize performance with PoE applications. The N238-001-GY-TF handles the frequent mating and unmating of surveillance cameras, VoIP phone systems, wireless access points and other PoE and PoE+ devices under electrical load.

**TAA-Compliant for GSA Schedule Purchases** The N238-001-GY-TF is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

### Highlights

- Keystone design compatible with wall plates, patch panels and surface-mount boxes
- RJ45 termination is quick and easy with no punchdown tools required
- PoE+ compliant jack is recommended for Cat6 premise wiring
- Specially designed to prevent spark-gap erosion that can affect transmission
- Includes shutter/dust cap to protect end from dust and debris when not in use

### Applications

- Connect a Cat5e/6 network with PoE+ devices mounted in areas that are difficult to reach or have no electrical outlets
- Set up indoor digital signage in offices, hotels, restaurants, bars, bus stations and airports

### Package Includes

- N238-001-GY-TF Keystone Jack Cat6/Cat5e, White, TAA
- Shutter/dust cap
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332236197
Technology	Cat5/5e; Cat6



<b>PHYSICAL</b>	
Color	White
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 13.97
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 5.50
Shipping Weight (kg)	0.01
Shipping Weight (lbs.)	0.02
Unit Dimensions (hwd / cm)	1.92 x 2.19 x 3.43
Unit Dimensions (hwd / in.)	0.76 x 0.86 x 1.35
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 to 140 F (-10 TO 60 C)
Storage Temperature Range	-40 to 154 F (-40 TO 68 C)
Relative Humidity	10% to 90% RH, Non-Condensing
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	110 IDC
PoE Type	Type 3 PoE++/UPoE (60W, IEEE 802.3bt)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>