


Safe-IT 4-Port Antibacterial Wall-Mount Insert, Decora Style, Vertical, Ivory, TAA

MODEL NUMBER: N042DAB-004V-IV



Decora-style insert combines with compatible wall-mount faceplate for terminating premise audio/video, voice or data cable applications.

Features

Decora-Style Insert Connects Audio/Video, Voice and Data Cable Lines at the Wall

This vertical-style center insert combines with a compatible Decora-style wall plate (sold separately) to complete an in-wall wiring application, such as home theater (audio/video), VoIP phones (voice) and Ethernet (data). Any type of keystone jack, including those used in HDMI, DisplayPort, RCA, USB and Cat5e/6/6a installations, snaps easily into the cutouts for quick cable connection.

Provides Extra Protection Against Certain Bacteria

The N042DAB-004V-IV is constructed using an antibacterial material that is effective in inhibiting *Escherichia coli* (E. coli) and *Staphylococcus aureus* (staph) and tested to ISO 22196:2011 standards. This added protection makes this cover plate an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This durable ivory-colored insert blends elegantly into any home or office décor for a sleek, professional installation. Mounting screws are included. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

TAA-Compliant for GSA Schedule Purchases

The N042DAB-004V-IV is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332269058
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB 2.0 (High Speed)
Country/Region	Global

Highlights

- Ideal for home theater, VoIP or Ethernet premise wiring installations
- Made with antibacterial material proven effective in inhibiting E. coli and staph
- Compatible with any type of keystone jack, including HDMI, Cat5/6, USB and DisplayPort
- High-impact plastic construction designed to blend in with your home/office decor
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- N042DAB-004V-IV 4-Port Antibacterial Wall-Mount Insert, Ivory
- (2) Mounting screws



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Number of Ports	4
Side A - Connector 1	(4) KEYSTONE JACK CUTOUT
PHYSICAL	
Color	Ivory
Material of Construction	Faceplate: ABS; Copper Pillars: Brass
Total Number of Ports	4
Unit Dimensions (hwd / in.)	0.350 x 5.000 x 7.750
Finish	Gloss
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
FEATURES & SPECIFICATIONS	
Antibacterial	Yes
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://triplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.