

1-Port European-Style Insert, Unloaded Shuttered Module, 22.5 x 45 mm, White

MODEL NUMBER: **N042E-WHM1-S**



European-style module accepts a compatible keystone jack for terminating premise audio/video, voice or data applications.

Features

European Shuttered Module Connects Your Audio/Video, Voice or Data Network

This European-style insert with unloaded shuttered module is ideal for your premise wiring applications, including home theater, VoIP phones and Ethernet. Just snap a keystone jack, including one used in HDMI, DisplayPort, RCA audio, USB and Cat5e/6/6a applications, into the module's cutout for immediate cable connection. The insert is compatible with Tripp Lite's N042E-WF1 wall plate.

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white module is shuttered to resist dust. It measures 22.5 x 45 millimeters and blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- High-impact plastic construction designed to blend in with your home/office décor
- White insert measures 22.5 x 45 mm for a sleek, professional appearance

Package Includes

N042E-WHM1-S 1-Port Europe-Style Insert, White

Specifications

OVERVIEW	
UPC Code	037332268877
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB 2.0 (High Speed)
Country/Region	Europe
PHYSICAL	
Color	White
Material of Construction	ABS
Total Number of Ports	1
Unit Dimensions (hwd / in.)	1.772 x 0.886 x 0.965



Finish	Matte
ENVIRONMENTAL	
Operating Temperature Range	14 TO 140 F (-10 to 60 C)
Storage Temperature Range	-40 TO 154.4 F (-40 to 68 C)
Operating Humidity Range	10% TO 90% RH, (NON-CONDENSING)
Storage Humidity Range	10% TO 90% RH, (NON-CONDENSING)
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	KEYSTONE JACK CUTOUT
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>