

## Double-Gang Surface Mounting Box, UK Style, 86 x 147 x 47 mm, White

MODEL NUMBER: **N042U-MB2**



Works with a compatible wall plate to complete in-wall audio/video, voice and Ethernet connections using any type of keystone jack.

### Features

#### UK-Style Back Box Connects Audio/Video, Voice and Data Cable Lines in Your Network

This double-gang box combines with a Tripp Lite or other compatible wall plate (sold separately) to complete a premise wiring application, such as home theater (audio/video), VoIP phone (voice) or Ethernet (data) network.

#### High-Impact Construction Designed to Blend In Seamlessly with Your Room

This durable white mounting box blends elegantly into any home or office décor for a sleek, professional installation. Mounting screws are included. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

#### Compatible with U.K. Applications

The N042U-MB2 is designed to work with standard double-gang wall plates measuring 86 x 147 millimeters. Compatible Tripp Lite models include N042U-WF2-2, N042U-WM1-S, N042U-WHM-S, N042U-WHM-SA and N042U-WF2-6C.

### Highlights

- Ideal for completing home theater, VoIP or Ethernet wiring installations
- High-impact plastic construction designed to blend in with your home/office décor

### Package Includes

- N042U-MB2 Double-Gang UK-Style Mounting Box, White
- (2) Mounting screws

## Specifications

OVERVIEW	
UPC Code	037332269362
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; USB 2.0 (High Speed); HDBaseT; HDMI; DisplayPort
Country/Region	UK
PHYSICAL	

Color	White
Material of Construction	ABS
Total Number of Ports	0
Unit Dimensions (hwd / in.)	5.768 x 3.386 x 1.850
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty