

## Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC) - Red, 10M (33 ft.)

MODEL NUMBER: N320-10M-RD



### Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- Red PVC jacket
- Length: 10 meter Connectors: LC connector on each end
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) and OFNR rated

## Specifications

OVERVIEW	
UPC Code	037332130808
Technology	Multimode
Optical Mode	OM1
PHYSICAL	
Cable Jacket Color	Red
Connector Color	Gray
Cable Jacket Material	LSZH
Cable Jacket Rating	OFNR
Clad Diameter (microns)	125
Core Diameter (microns)	62.5
Number of Fibers	2

### Highlights

- Manufactured from 62.5/125 duplex (Zipcord) fiber with Red jacket
- Length: 10 meter Connectors: LC connector on each end
- Insertion loss testing performed on every connector (0.2dB typical)

### System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors

### Package Includes

- 10M Duplex MMF Cable LC/LC 62.5/125 Micron Fiber Red Jacket



Cable Length (ft.)	32.8
Cable Length (m)	10.00
Cable Length (in.)	393.7
Minimum Bend Radius	20MM (Dynamic); 10MM (Static)
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.75
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.90
Shipping Weight (lbs.)	0.12
Shipping Weight (kg)	0.06
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 to 140 °F (-20 to 60 °C)
Storage Temperature Range	-4 to 140 °F (-20 to 60 °C)
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 65% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Network Compatibility	1 Gbps (Gigabit); 10 Gbps
Attenuation @ 850NM	3.0dB/Km
Insertion Loss	0.20dB
<b>CONNECTIONS</b>	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	LC DUPLEX (MALE)
Endface Polish	PC
<b>FEATURES &amp; SPECIFICATIONS</b>	
Push/Pull Tabs	No
Breakout	No
Trunk	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>