


1-Port Single Gang Faceplate, Stainless Steel, Industrial Grade, IP44, TAA

MODEL NUMBER: N206-FP01-IND



Bulkhead wall plate combines with a coupler and industrial Cat5e/6, USB 3.0 or 4K HDMI cable to complete an IP44 connection.

Features

Bulkhead Wall Plate Recommended for Outdoor or Harsh Indoor Environments This single-gang industrial bulkhead face plate is ideal for connecting Cat5e/6 networks, USB 3.0 or 4K HDMI installations in outdoor applications and other areas where protection from harsh elements is essential. The stainless steel frame and rubber back gasket contribute to the wall plate's IP44 rating, which ensures protection from splashing water from all directions. Wall-mounting hardware is included.

Designed for Use with Industrial-Grade Cables and Couplers The Bulkhead wall plate with one cutout is recommended for use with N206-Series industrial Cat5e/6 patch cables and N206-BC01-IND bulkhead coupler or N206-KJ01-IND keystone jack, the U325-Series industrial USB 3.0 cables and U325-000-IND bulkhead coupler and the P569-000-FF-IND bulkhead coupler and P569-Series industrial 4K HDMI cables (all sold separately).

TAA-Compliant for GSA Schedule Purchases The N206-FP01-IND is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Lifetime Warranty The N206-FP01-IND is backed by a lifetime warranty, ensuring reliability and performance.

Highlights

- Built to protect Gigabit Ethernet and digital signage applications in harsh environments
- IP44-rated to prevent splashing water from damaging cables and other equipment
- Designed for industrial cables and couplers—no guessing about compatibility
- Wall-mounting hardware included for immediate installation
- Complies with Federal Trade Agreements Act standards for GSA Schedule purchases

Applications

- Connect Gigabit Ethernet networks, security cameras or digital signage in factories, warehouses, recycling plants, machine shops and other industrial environments
- Provide Cat6, USB 3.0 or 4K HDMI connectivity in outdoor environments susceptible to rain, such as a stadium or outdoor arena
- Set up outdoor digital signage at malls, theaters and bus stops

Package Includes

- N206-FP01-IND Bulkhead Wall Plate, 1 Cutout, Industrial, Metal
- (2) Wall-mounting screws
- (2) Washers
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332206251
Technology	Cat5/5e; Cat6
Country/Region	Global
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

Number of Ports	1
PHYSICAL	
Color	Silver
Included Mounting Accessories	SCREW (X2), SCREW WASHER (X2)
Total Number of Ports	1
Shipping Dimensions (hwd / in.)	7.70 x 5.00 x 0.50
Shipping Dimensions (hwd / cm)	19.56 x 12.70 x 1.27
Shipping Weight (lbs.)	0.18
Shipping Weight (kg)	0.08
FEATURES & SPECIFICATIONS	
Antibacterial	No
Snagless Connector	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.