

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks

10G Duplex Multimode 50/125 OM3 LSZH Fiber Optic Cable (LC/LC), Aqua, 2M (6.56 ft.)

MODEL NUMBER: **N820-02M**



Highlights

- OM3 rated for 10G Ethernet applications
- Low-smoke, zero halogen (LSZH) aqua-colored jacket
- Max 10G distance of 300 m @ 850 nm
- Backward compatible with existing 50/125 fiber

Package Includes

- N820-02M 10G Duplex Multimode Fiber Optic Cable (LC/LC), Aqua, 2 m

Features

- OM3-rated 2 m (6 ft.) cable with LC/LC connectors
- 10G Ethernet speeds to 300 m @ 850 nm
- High speed, high bandwidth, low cost
- Ideal for fibre channel (SAN) applications
- IEEE 802.3ae and TIA LOMMF compliant
- Use with VCSEL and LED laser light sources
- Backward compatible with legacy LANs

Specifications

OVERVIEW	
UPC Code	037332134660
Clad Diameter	125 micron
Core Diameter	50 micron
Number of Fibers	2
Technology	Multimode
Optical Mode	OM3
INPUT	
Cable Length (ft.)	6.6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	2
Cable Length (in.)	78.7
PHYSICAL	
Cable Jacket Rating	LSZH
Color	Aqua
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.03
Shipping Weight (lbs.)	0.06
COMMUNICATIONS	
Network Speed	10Gbps / 40Gbps / 100Gbps
CONNECTIONS	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	LC DUPLEX (MALE)
SPECIAL FEATURES	
Push/Pull Tabs	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>