

24-Port Cat6/Cat5 Low Profile Feed-Through Patch Panel, 1U Rack-Mount/Wall-Mount, TAA

MODEL NUMBER: N250-024-LP



Easy Cat6 Cable patching with right-angle couplers

Description

Tripp Lite's N250-024-LP, Cat6 Feed-Through Low Profile patch panel, makes cable patching quick and easy, by simply plugging Cat6 patch cables into either side of the Cat6 couplers. Ninety degree angles on the couplers allows for low profile mounting to a wall with included stand-off brackets. Cables feed into the front of the panel, and corresponding patch cables exit Up, Down, Left, or Right, depending on the mounting position. Patented printed circuit board design within the coupler exceeds NEXT requirements for Cat6 component testing, assuring Gigabit+ speeds.

UTP Cat6 Patch Cord

Features

- 24-port Feed-through panel for Cat6 or Cat5e networks
- Wall or Rack mountable (standoff brackets included for wall mounting)
- 19" Wide by 1.75" (1U) High x 1.42" deep
- Ninety degree coupler allows a multitude of mounting angle options
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332171139
Technology	Cat5/5e; Cat6
PHYSICAL	
Color	Black

Highlights

- 90 degree Cat6 RJ45 jacks allows easy cable routing
- Wall mountable with standoff brackets, or rack mountable
- Exceeds TIA-EIA-568-C.2 Cat6 Component requirement
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

24-port Cat6 Low Profile Feed-Through Patch Panel



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	6.35 x 7.62 x 49.78
Shipping Dimensions (hwd / in.)	2.50 x 3.00 x 19.60
Shipping Weight (kg)	0.77
Shipping Weight (lbs.)	1.70
CONNECTIONS	
Ports	24
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>