

## Cat6a 10G Certified Snagless UTP Ethernet Cable (RJ45 M/M), Aqua, 14 ft. (4.27 m)

MODEL NUMBER: N261-014-AQ



### Highlights

- Next Generation Cat6 - CAT6a ( Augmented )
- 10Gbps Over Copper to 100mtr
- Each cable Fluke® Tested and Verified
- 14-ft. (4.27 m) cable

### Package Includes

- 14ft Cat6a Aqua Patch Cable

### Features

- 14-ft. (4.27 m) 10Gig over copper patch cable
- 100% FLUKE® tested and certified
- ETL/UL Verified
- Supports IEEE 802.3af and is DTE power compliant
- Backward compatible with all previous 10BaseT generations
- New Cat6 RJ45 plug improves NEXT performance to 500Mhz
- 24ga, 4pr, Stranded PVC cable
- Compatible with T568A and T568B wiring
- Easy disconnect snagless hood
- PoE rated to four times the standard

## Specifications

OVERVIEW	
UPC Code	037332131720
Technology	Cat6a
INPUT	
Cable Length (ft.)	14
Cable Length (m)	4.3
Cable Length (in.)	168



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Cable Length (cm)	426.7
<b>PHYSICAL</b>	
Cable Shielding	UTP
Color	Aqua
Shipping Dimensions (hwd / cm)	1.27 x 15.24 x 17.78
Shipping Dimensions (hwd / in.)	0.50 x 6.00 x 7.00
Shipping Weight (kg)	0.20
Shipping Weight (lbs.)	0.45
Snagless Connector	Yes
Wire Type	Stranded
<b>COMMUNICATIONS</b>	
Network Speed	10Gbps
<b>CONNECTIONS</b>	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>