

SFP+ 10GBASE-CU Passive Twinax Copper Cable, SFP-H10GB-CU50CM Compatible, Black, 20-in. (50.8 cm)

MODEL NUMBER: N280-20N-BK



Features

- 20-in. (50.8 cm) 30 AWG SFP+ high-speed passive copper cable is fully compliant to MSA SFF-8431 specification
- Supports 1x, 2x, 4x and 8x Fiber Channel data rates
- Low-power equivalence to Cisco SFP-H10GB-CU1-5M
- Ideal for 10G Ethernet and Fibre Channel applications
- 100-ohm twinaxial cable with die-cast metal shells and pull-tab latches

Highlights

- 20-in. (50.8 cm) 30 AWG SFP+ high-speed passive copper cable for 10G Ethernet applications
- Complies with MSA SFF-8431 specs
- Equivalent to Cisco SFP-H10GB-CU1-5M
- An excellent low-cost alternative to fiber optic cabling

System Requirements

- Conforms to SFF-8431 standards and can be used with manufacturers' equipment open to third-party cables, including ARISTA, BROADCOM, CISCO, DELL, EMC, EMULEX, EXTREME, FINISAR, IBM, JUNIPER, QLOGIC and VOLTAIRE
- Confirmed equipment list (with updated firmware and software): CISCO NEXUS, CISCO CATALYST, CISCO CATALYST 3750x, CISCO CATALYST 2960, CISCO CATALYST 3500, CISCO CATALYST 3550, CISCO NEXUS 5010, ARISTA 70505-64, QUANTA T3048, EXTREME X250E, JUNIPER EX3200
- Not compatible with third-party cables: HP, BROCADE

Package Includes

- N280-20N-BK SFP+ High-Speed Passive Copper Cable,



10 Gbps, 30 AWG, Black, 20-in.
(50.8 cm)

Specifications

OVERVIEW	
UPC Code	037332178213
Technology	SFP+/QSFP+/QSFP28
INPUT	
Cable Length (ft.)	1.7
Cable Length (m)	0.51
Cable Length (in.)	19.68
Cable Length (cm)	49.9872
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	30.48 x 26.67 x 1.27
Shipping Dimensions (hwd / in.)	12.00 x 10.50 x 0.50
Shipping Weight (kg)	0.08
Shipping Weight (lbs.)	0.18
CONNECTIONS	
Side A - Connector 1	SFP+ (MALE)
Side B - Connector 1	SFP+ (MALE)
STANDARDS & COMPLIANCE	
Certifications	RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>