

## Power Extension Cord, NEMA 5-15P to NEMA 5-15R - 10A, 120V, 18 AWG, 25 ft. (7.62 m), Black

MODEL NUMBER: P022-025



25-foot extension cord connects two devices with 5-15P/5-15R power connectors or extends your existing power connection.

### Features

**25-ft. (7.62 m) Extension Cord Connects Computers, Printers, Servers and Other Equipment** This power extension cable is designed for small data center or office workstation applications that do not require a heavy-gauge connection. With a NEMA 5-15P plug on one end and a NEMA 5-15R receptacle on the other, this cord can be used to power a computer, printer or monitor; attach a rack server to a UPS system or PDU; or extend an existing connection up to 25-ft. (7.62 m). The 25-ft. (7.62 m) length allows you great flexibility in placing equipment with respect to the power outlet.

### Highlights

- Recommended for powering computers, monitors and other essential peripherals
- Adds 25-ft. (7.62 m) to your existing connection to provide more flexibility in placing devices
- Ideal replacement for worn-out or missing 25-ft. (7.62 m) extension cord

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 25-ft. (7.62 m) away in your data center
- Extend an existing power connection up to 25-ft. (7.62 m) to more easily place a device or reach a power source away from your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P022-025 Power Extension Cord, NEMA 5-15P to NEMA 5-15R, 25-ft. (7.62 m), Black

## Specifications

OVERVIEW	
UPC Code	037332164872
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>INPUT</b>	
Maximum Input Amps	10
Voltage Compatibility (VAC)	120
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	25
Cable Length (m)	7.6
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	3.81 x 27.94 x 38.10
Shipping Dimensions (hwd / in.)	1.50 x 11.00 x 15.00
Shipping Weight (kg)	0.77
Shipping Weight (lbs.)	1.70
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
<b>SPECIAL FEATURES</b>	
High Voltage	No
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>