

## C20 to C13 Power Cord for Computer - Heavy Duty, 15A, 100-250V, 14 AWG, 3 ft., Black

MODEL NUMBER: P032-003



C20-to-C13 adapter connects devices with C19/C14 power connectors or extends your existing power connection by 3 ft.

### Features

**Heavy-Duty Computer Power Cord for Devices That Require a Heavy-Gauge Connection** This C20-to-C13 power cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This IEC C20-to-C13 cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

### Highlights

- Recommended for powering computers, servers and other network devices
- 3 ft. length allows flexibility in placing devices, while avoiding cable clutter
- Heavy-duty C13-to-C20 cable replaces or upgrades standard cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 3 ft. away in your data center
- Extend an existing power connection up to 3 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P032-003 C20 to C13 Power Cable for Computer, 3 ft., Black

## Specifications

OVERVIEW	
UPC Code	037332190123
Country/Region	North America
INPUT	



Maximum Input Amps	15
Cable Length (ft.)	3
Cable Length (m)	0.9
Voltage Compatibility (VAC)	100-250
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJTW
Shipping Dimensions (hwd / cm)	22.50 x 32.51 x 1.27
Shipping Dimensions (hwd / in.)	8.86 x 12.80 x 0.50
Shipping Weight (kg)	0.26
Shipping Weight (lbs.)	0.57
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	3.31
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C13
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>