

## UK Computer Power Cord - BS1363 to C5, 2.5A, 250V, 18 AWG, 6 ft. (1.8 m), Black

MODEL NUMBER: P060-006



UK computer power cord connects your computer or peripheral with a C6 inlet to any grounded AC power outlet that accepts BS1363 plugs.

### Features

**UK Plug to C5 Power Cord Connects Notebook Computers to a BS1363 AC Outlet** This UK computer power cable is designed for connecting a notebook computer, laptop or other device with a three-slot C6 inlet to a UPS system, PDU or other BS1363 outlet. It is also a durable replacement for a worn-out or lost laptop power cord. The six-foot (1.8-meter) length allows you flexibility in placing equipment with respect to the power outlet.

### Highlights

- UK computer power cable for powering notebooks and laptops with C6 inlets
- 6 ft. (1.8 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing UK IEC power cord

### Applications

- Connect a laptop or notebook computer to a PDU up to 6 ft. (1.8 m) away in your workstation
- Extend an existing power connection up to 6 ft. (1.8 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P060-006 BS1363 to C5 UK Computer Power Cable, 6 ft. (1.8 m), Black

## Specifications

OVERVIEW	
UPC Code	037332153630
Country/Region	UK
INPUT	
Maximum Input Amps	2.5
Cable Length (ft.)	6
Cable Length (m)	1.8
Voltage Compatibility (VAC)	250



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	23.01 x 18.01 x 1.27
Shipping Dimensions (hwd / in.)	9.06 x 7.09 x 0.50
Shipping Weight (kg)	0.21
Shipping Weight (lbs.)	0.46
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	1.02
<b>CONNECTIONS</b>	
Side A - Connector 1	BS1363 UK PLUG
Side B - Connector 1	IEC-320-C5
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>