

DVI to VGA Y Splitter Adapter Cable (DVI-I-M to 2x HD15-F), 1 ft.

MODEL NUMBER: P120-001-2



Ideal for conference rooms and sales presentations where two VGA monitors or projectors must be simultaneously fed from a single DVI-I signal while delivering superior video quality.

Description

Tripp Lite's P120-001-2 DVI to 2 x VGA splitter allows you to attach two VGA enabled devices, such as monitors and projectors, to your computer's DVI-I port. DVI-I enabled computers are capable of outputting both Analog and Digital signals, so the splitter is perfect for connecting VGA LCD monitors, projectors simultaneously. (For splitting to two DVI-enabled monitors, use Tripp Lite P564-001). Fully molded construction and double-shielding ensures long life and high performance. Supports video resolutions up to 2048 x 1536.

Features

- Connect two VGA monitors to a single DVI-I port
- 1 ft. DVI-A Analog Male to 2 x VGA (HD15) Female Cable
- Fully molded construction and double-shielding ensures long life
- Superior video quality; supports video resolutions up to 2048 x 1536
- RoHS Compliant

Specifications

OVERVIEW	
UPC Code	037332142238
Technology	DVI; VGA/SVGA
INPUT	

Highlights

- Splits a DVI-A Analog signal to connect two VGA-enabled devices to a single DVI-I port
- Ideal solution when you need to display a video signal to 2 monitors for presentations.
- Fully molded construction and double-shielding guarantees long life
- Superior video quality; supports video resolutions up to 2048 x 1536

System Requirements

- DVI-I enabled computer (supports both Analog and Digital)

Package Includes

- 1 ft. DVI-A Analog Male to 2 x VGA (HD15) Female Cable



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	1
Cable Length (m)	0.3
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
CONNECTIONS	
Side A - Connector 1	DVI-A (MALE)
Side B - Connector 1	(2) HD15 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>