

DisplayPort to HDMI 4K 60Hz Active Adapter (M/F), Latching Connector, Black, DP1.2, HDCP 2.2, 6 in.

MODEL NUMBER: P136-06N-H2V2LB



Connects your DisplayPort (DP) laptop to a 4K HDMI monitor, projector or HDTV for crystal-clear video and audio.

Features

More Convenient, Less Expensive Way to Watch 4K Video This DisplayPort to HDMI active converter expands the potential of your DP computer or laptop by allowing it to transmit UHD video and audio to a 4K monitor, projector or HDTV. This allows you to continue using your existing HDMI display with a DisplayPort 1.2 source device.

Latching DisplayPort Plug Provides a Secure Connection The molded DP connector features special latches, which help prevent the DP to HDMI adapter from becoming loose or accidentally dislodged from the source device and causing signal loss.

Outstanding 4K x 2K Picture Quality at 60 Hz This adapter cable supports HDMI bandwidth up to 18 Gbps, allowing you to enjoy 4K video on a large HDMI monitor or digital sign. It supports video resolutions up to 4K at 60 Hz (3840 x 2160) as specified in HDMI 2.0 and DisplayPort 1.2 audio (if your DP card supports audio pass through). It is backward compatible with all previous HDMI versions.

Ready to Use Right Out of the Package The plug-and-play DisplayPort to HDMI active converter requires no software, drivers or external power. It's compatible with both Single- and Dual-Mode (DP++) DP output, and recommended for use with graphics cards that do not output DP++ signals. The compact unit fits easily into a briefcase or laptop bag for connecting on the go.

Premium Construction for Premium Performance Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded connectors with corrosion-resistant gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief reduces stress and helps the cable and connectors move freely without cracking.

3-Year Warranty and Environmentally Responsible Design The P136-06N-H2V2LB comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- Keep using your current HDMI display with a DisplayPort 1.2 source
- Delivers outstanding picture quality at video resolutions up to 4K x 2K @ 60 Hz as specified in HDMI 2.0
- Latching DP connector prevents cable from becoming accidentally dislodged
- Compact unit fits easily into briefcase or laptop bag for immediate use anywhere
- Easy installation with plug-and-play operation—no software required

Applications

- Play video from your DP laptop or PC on a 4K HDMI display device, such as an HDTV
- Access documents and websites across multiple displays
- Design and edit graphics files or production video on a larger HDMI monitor
- Look at high-definition photos from your DP computer on a flat-screen HDMI TV
- Display menus, ads, promos, directions and other digital signage applications on an HD monitor

System Requirements

- Source device with DisplayPort output
Display device with HDMI



input

- DisplayPort 1.2 and HDMI 2.0 required for 4K resolution @ 60 Hz

Package Includes

- P136-06N-H2V2LB DisplayPort to HDMI 2.0 Adapter-M/F, Latching Connector, 4K, 6 in., Black

Specifications

OVERVIEW	
UPC Code	037332209238
Technology	HDMI; DisplayPort
INPUT	
Cable Length (ft.)	0.5
Cable Length (in.)	6
Cable Length (cm)	15.24
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.triplite.com/products/product-certification-agencies>