

## DisplayPort to HDMI 4K Active Adapter Video Converter, DP Ver 1.2, HDCP, 4K 30Hz (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P136-06N-UHD-V2



Converts a DisplayPort 1.2 audio and 4K x 2K video signal for display on an HDMI monitor, projector or television.

### Features

#### Send High-Quality DisplayPort 1.2 Audio/Video Signals to an HDMI Display

- Connects DisplayPort 1.2 computer to HDMI-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Female HDMI and male DisplayPort connectors
- Backward compatible with previous DisplayPort generations

#### Vibrant, Superior Video Quality

- Supports Ultra High Definition (UHD) video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports 7.1 Audio Surround Sound
- HDCP 1.3 and DPCP 1.0 compliant
- Converts both Single-Mode and Dual-Mode DisplayPort output
- Works with graphics cards that don't output DP++ signals, such as AMD Eyefinity

#### Superior Materials for Superior Performance

- Gold-plated connectors and contacts for excellent conductivity
- Integral strain relief for long life
- Plug-and-play—no software, drivers or power supply necessary
- Fits easily into briefcase, backpack or laptop bag

### Highlights

- Active converter works with all DisplayPorts
- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports 7.1 Audio Surround Sound
- HDCP 1.3 and DPCP 1.0 compliant
- Converts both Single-Mode and Dual-Mode DisplayPort output
- Gold-plated connectors and contacts

### Package Includes

- P136-06N-UHD-V2 DisplayPort 1.2 to HDMI Active Converter (M/F), 6 in.



## Specifications

<b>OVERVIEW</b>	
UPC Code	037332192028
Technology	HDMI; DisplayPort
<b>PHYSICAL</b>	
Color	Black
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Weight (kg)	0.04
Shipping Weight (lbs.)	0.09
<b>CONNECTIONS</b>	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	1.3
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>