

Power Extension Cord, NEMA L5-30P to NEMA L5-30R- Heavy-Duty, 30A, 125V, 10 AWG, 15 ft. (4.57 m), Black, Locking Connectors

MODEL NUMBER: P046-015-LL-30A



Heavy-duty extension cord connects your computer or other device with a NEMA L5-30P plug to a NEMA L5-30R outlet.

Features

Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection This cord features 10 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, server or other device with a NEMA L5-30P plug to a wall outlet, PDU or UPS system with a NEMA L5-30R outlet. The 15-ft. (4.57 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Locking Connectors Help Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. Locking connectors on each end help you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Highlights

- Recommended for powering computers, servers and other network devices
- 15-ft. (4.57 m) length allows great flexibility in placing devices in relationship to AC outlet
- Heavy-duty cord replaces or upgrades standard power cord provided by manufacturer
- Thick 10 AWG wire gauge manages high power levels required for larger equipment
- Locking connectors maintain secure link to avoid loss of power and costly downtime

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 15-ft. (4.57 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P046-015-LL-30A L5-30P to L5-30R Heavy-Duty Extension Cord, 15-ft. (4.57 m), Black, Locking Connectors

Specifications



| OVERVIEW | |
|------------------------------------|----------------------------|
| UPC Code | 037332200952 |
| Device Compatibility | UPS; PDU |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 30 |
| Cable Length (ft.) | 15 |
| Cable Length (m) | 4.6 |
| Cable Length (in.) | 180 |
| Voltage Compatibility (VAC) | 125 |
| Cable Length (cm) | 457.20 |
| PHYSICAL | |
| Wire Gauge (AWG) | 10 |
| Wire Gauge (OD - mm ²) | 5.26 |
| Color | Black |
| Number of Conductors | 3 |
| Power Cord Jacket Type | SJT |
| Shipping Dimensions (hwd / cm) | 1.27 x 26.16 x 37.34 |
| Shipping Dimensions (hwd / in.) | 0.50 x 10.30 x 14.70 |
| Shipping Weight (kg) | 1.81 |
| Shipping Weight (lbs.) | 4.00 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 41 F TO 95 F (5 C TO 35 C) |
| Storage Temperature Range | 41 F TO 95 F (5 C TO 35 C) |
| Operating Humidity Range | 0-65% RH |
| Storage Humidity Range | 0-65% RH |
| CONNECTIONS | |
| Side A - Connector 1 | NEMA L5-30P |
| Side B - Connector 1 | NEMA L5-30R |
| SPECIAL FEATURES | |
| High Voltage | No |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|---------------------------|
| Locking Plug | Yes |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>