

Keyspan Mini DisplayPort to HDMI Active Adapter Video Converter (M/F) - 4K, DP1.2, 6 in.

MODEL NUMBER: P137-06N-HD-UHD



Connect a UHD 4K x 2K HDMI monitor to a Mac or PC with a Mini Displayport output

Features

- Connect a UHD HDMI TV to a Mac or PC with a Mini Displayport output
- Active adapter for use with any Mini Displayport (or Thunderbolt 1 & 2) port
- Converts Single-Mode and Dual-Mode (DP++) Mini DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals
- Plug-and-play operation with no software required for easy, immediate installation
- Supports Ultra High Definition (UHD) video resolutions up to 4K x 2K (3840 x 2160) @ 24/30 Hz
- HDCP compliant
- Transmits an audio signal as long as it is supported by the Mini DisplayPort; check the documentation for your Mini DisplayPort source for compatibility

Highlights

- Connect a UHD HDMI monitor to a Mac or PC with a Mini Displayport output
- Active adapter for use with any Mini Displayport (or Thunderbolt 1 & 2) port
- Plug-and-play convenience—no drivers or software needed
- Supports Ultra High Definition (UHD) video resolutions up to 4Kx2K, 3840 x 2160 (24Hz or 30Hz)
- HDCP compliant

System Requirements

- Computer with a Mini DisplayPort (or Thunderbolt 1 & 2) port
- Monitor with a HDMI port
- 7.1 Audio Surround Sound is supported as long as it is supported by the source. Check your Mini DisplayPort source documentation for compatibility.
- Requires that the connected computer has a DP++ (DisplayPort ++) port, which allows HDMI and DVI signals to be passed through. Check your Mini DisplayPort source documentation for compatibility.

Package Includes

- P137-06N-HD-UHD Keyspan Mini DisplayPort 1.2 to UHD 4K HDMI Active Adapter/Video Converter (M/F), 6 in.

Specifications

OVERVIEW	
UPC Code	037332183910
Technology	HDMI; DisplayPort
VIDEO	
Max Supported Color Depth	36-bit Deep Color
PHYSICAL	
Color	White



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	9.00 x 0.50 x 7.00
Shipping Dimensions (hwd / cm)	22.86 x 1.27 x 17.78
Shipping Weight (lbs.)	0.26
Shipping Weight (kg)	0.12
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>