

Keyspan Mini DisplayPort to VGA/DVI/HDMI All-in-One Video Converter Adapter, 4K 30Hz HDMI, DP1.2, Black, 6-in. (15.24 cm)

MODEL NUMBER: P137-06N-HDV-4K



All-in-one converter/adapter connects your Mini DisplayPort-enabled laptop or tablet to a VGA, DVI or HDMI display without the need to carry separate adapters. Ideal for trade shows, classrooms and lecture halls.

Features

Connects Your Mini DisplayPort Laptop or Tablet to a VGA, DVI or HDMI Display

- Recommended for trade shows, classrooms, lecture halls and other presentations
- DVI port supports video resolutions up to 1920 x 1080 (1080p)
- HD15 port supports video resolutions up to 1920 x 1200, including 1080p
- HDMI port supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports 36-bit Deep Color (12 bits per channel)
- Ideal for Chromebooks, MacBooks, Microsoft Surface and laptops equipped with Mini DisplayPort or Thunderbolt 1 & 2 ports

Plug-and-Play Convenience

- No software, drivers or external power supply required
- Small enough to stow in laptop bag or briefcase
- Passive adapter requires connected computer to have DP++ port

Specifications

OVERVIEW	
UPC Code	037332190833
Product Type	Video Adapter
Technology	DVI; HDMI; VGA/SVGA; DisplayPort

Highlights

- Separate DVI, HD15 and HDMI female connectors
- HDMI port supports UHD 4K x 2K @ 24/30 Hz video resolutions
- Passive adapter requires connected computer to have DP++ port
- Plug and play—no software, drivers or power supply needed
- Small size for easy carrying in laptop bag or briefcase

System Requirements

- Passive adapter requires the connected computer to have a DP++ (Displayport ++) port

Package Includes

- P137-06N-HDV-4K Mini DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter, 6 in.
- Owner's manual

PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	3.94 x 5.51 x 0.91
Shipping Dimensions (hwd / cm)	10.01 x 14.00 x 2.31
Shipping Weight (lbs.)	0.16
Shipping Weight (kg)	0.07
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty