

EU Computer Power Cord , C19 to Schuko - 16A, 250V, 16 AWG, 8 ft. (2.43 m), Black

MODEL NUMBER: P050-008



IEC 320 C19 to Schuko EU power cord transforms a C20 plug into a Schuko plug for connecting to a wall outlet, PDU or UPS system.

Features

C19 to Schuko EU Power Cord Connects Computers, Servers and Other Network Devices This C19 to Schuko European power cord is designed for small data center or office workstation applications that do not require a heavy-gauge connection. The cable can be used to connect a computer, server or drive to a Schuko wall outlet, UPS system or PDU or replace or upgrade a worn-out or lost power cable. The 8-ft. (2.43 m) length allows you flexibility in placing equipment with respect to the power outlet.

Highlights

- C19 to Schuko cable for powering computers, servers and other network devices
- 8-ft. (2.43 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing EU power cable

Applications

- Connect devices like computers, servers and drives to a PDU up to 2.4 m away in your data center
- Transform a C20 plug into a Schuko plug with no electrician needed
- Extend an existing power connection up to 2.4 m to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P050-008 C19 to Schuko, EU Power Cord, 8-ft. (2.43 m), Black

Specifications

OVERVIEW	
UPC Code	037332141989
Device Compatibility	Computer; Server; UPS; PDU
Country/Region	Europe



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Maximum Input Amps	16
Cable Length (ft.)	8
Cable Length (m)	2.4
Voltage Compatibility (VAC)	250
PHYSICAL	
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.29
Color	Black
Number of Conductors	2
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	1.27 x 22.61 x 31.75
Shipping Dimensions (hwd / in.)	0.50 x 8.90 x 12.50
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
CONNECTIONS	
Side A - Connector 1	CEE 7/7 SCHUKO PLUG
Side B - Connector 1	IEC-320-C19
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>