

## Keyspan Mini DisplayPort to VGA/DVI/HDMI All-in-One Video Converter Adapter, 4K 60 Hz HDMI, DP 1.2, White, 6 in.

MODEL NUMBER: P137-06N-HDV4K6



All-in-one converter/adapter connects your Mini DisplayPort- or Thunderbolt-enabled laptop or tablet to a VGA, DVI or HDMI display without the need to carry separate adapters.

### Features

**Connects Your Mini DisplayPort Laptop or Tablet to a VGA, DVI or HDMI Display** Recommended for trade shows, classrooms, lecture halls and other presentation venues  
**DVI port** supports video resolutions up to 1920 x 1080 (1080p)  
**HD15 port** supports video resolutions up to 1920 x 1200, including 1080p  
**HDMI port** supports video resolutions up to 4K x 2K (3840 x 2160) @ 60 Hz, as specified in HDMI 2.0  
**Supports 36-bit Deep Color** (12 bits per channel)  
**Supports HDCP 2.2**

**Plug-and-Play Convenience** No software, drivers or external power supply required  
 Small enough to stow in laptop bag or briefcase

## Specifications

OVERVIEW	
UPC Code	037332202758
Technology	DVI; HDMI; VGA/SVGA; DisplayPort
PHYSICAL	
Color	White
Cable Length (in.)	6
Shipping Dimensions (hwd / in.)	0.91 x 5.51 x 3.94
Shipping Dimensions (hwd / cm)	2.31 x 14.00 x 10.01
Shipping Weight (lbs.)	0.13

### Highlights

- Separate DVI, HD15 and HDMI female connectors
- HDMI port supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Supports HDCP 2.2
- Plug-and-play operation with no software required for easy, immediate installation
- Small size for easy carrying in laptop bag or briefcase

### System Requirements

- Computer or tablet with Mini DisplayPort or Thunderbolt 1/2 output
- Display device with VGA, DVI or HDMI input

### Package Includes

- P137-06N-HDV4K6 Keyspan Mini DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter, 6 in.
- Owner's manual

Shipping Weight (kg)	0.06
<b>CONNECTIONS</b>	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	2.2
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty