

# Keyspan Mini DisplayPort to VGA/DVI/HDMI All-in-One Video Converter Adapter, 4K 60 Hz HDMI, DP 1.2, White, 6 in.

MODEL NUMBER: P137-06N-HDV4K6



All-in-one converter/adapter connects your Mini DisplayPort- or Thunderbolt-enabled laptop or tablet to a VGA, DVI or HDMI display without the need to carry separate adapters.

## Features

**Connects Your Mini DisplayPort Laptop or Tablet to a VGA, DVI or HDMI Display** Recommended for trade shows, classrooms, lecture halls and other presentation venues  
 DVI port supports video resolutions up to 1920 x 1080 (1080p)  
 HD15 port supports video resolutions up to 1920 x 1200, including 1080p  
 HDMI port supports video resolutions up to 4K x 2K (3840 x 2160) @ 60 Hz, as specified in HDMI 2.0  
 Supports 36-bit Deep Color (12 bits per channel)  
 Supports HDCP 2.2

**Plug-and-Play Convenience** No software, drivers or external power supply required  
 Small enough to stow in laptop bag or briefcase

## Highlights

- Separate DVI, HD15 and HDMI female connectors
- HDMI port supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Supports HDCP 2.2
- Plug-and-play operation with no software required for easy, immediate installation
- Small size for easy carrying in laptop bag or briefcase

## System Requirements

- Computer or tablet with Mini DisplayPort or Thunderbolt 1/2 output
- Display device with VGA, DVI or HDMI input

## Package Includes

- P137-06N-HDV4K6 Keyspan Mini DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter, 6 in.
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332202758
Technology	DVI; HDMI; VGA/SVGA; DisplayPort
PHYSICAL	
Color	White
Cable Length (in.)	6
Shipping Dimensions (hwd / cm)	2.31 x 14.00 x 10.01
Shipping Dimensions (hwd / in.)	0.91 x 5.51 x 3.94



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Weight (kg)	0.06
Shipping Weight (lbs.)	0.13
<b>CONNECTIONS</b>	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	2.2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>