

## European Computer Power Cord, C13 to Schuko, 10A, 250V, 17 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P054-006



IEC 320 C13 to Schuko EU power cord transforms a C14 plug into a Schuko plug for connecting to a wall outlet, PDU or UPS system.

### Features

**C13 to Schuko EU Power Cord Connects Computers, Servers and Other Network Devices** This Schuko to C13 European computer power cord is designed for small data center or office workstation applications that do not require a heavy-gauge connection. The cable can be used to connect a computer, server or drive to a Schuko wall outlet, UPS system or PDU or replace or upgrade a worn-out or lost power cable. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

### Highlights

- C13 to Schuko cable for powering computers, servers and other network devices
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing EU power cable

### Applications

- Connect devices like computers, monitors and printers to a PDU up to 1.8 m away in your home or office workstation
- Transform a C14 plug into a Schuko plug with no electrician needed
- Extend an existing power connection up to 1.8 m to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P054-006 C13 to Schuko, European Computer Power Cord, 6 ft. (1.8 m), Black

## Specifications

OVERVIEW	
UPC Code	037332145574
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	Europe



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>INPUT</b>	
Maximum Input Amps	10
Voltage Compatibility (VAC)	250
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	17
Wire Gauge (OD - mm <sup>2</sup> )	1.15
Cable Length (ft.)	6
Cable Length (m)	1.8
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	32.51 x 22.61 x 1.27
Shipping Dimensions (hwd / in.)	12.80 x 8.90 x 0.50
Shipping Weight (kg)	0.23
Shipping Weight (lbs.)	0.50
<b>CONNECTIONS</b>	
Side A - Connector 1	CEE 7/7 SCHUKO PLUG
Side B - Connector 1	IEC-320-C13
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>