

## UK Computer Power Cord - BS1363 to C5, 2.5A, 250V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P060-006



UK computer power cord connects your computer or peripheral with a C6 inlet to any grounded AC power outlet that accepts BS1363 plugs.

### Features

**UK Plug to C5 Power Cord Connects Notebook Computers to a BS1363 AC Outlet** This UK computer power cable is designed for connecting a notebook computer, laptop or other device with a three-slot C6 inlet to a UPS system, PDU or other BS1363 outlet. It is also a durable replacement for a worn-out or lost laptop power cord. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

## Specifications

| OVERVIEW                    |                            |
|-----------------------------|----------------------------|
| UPC Code                    | 037332153630               |
| Device Compatibility        | Laptop; Computer; UPS; PDU |
| Country/Region              | UK                         |
| INPUT                       |                            |
| Maximum Input Amps          | 2                          |
| Voltage Compatibility (VAC) | 100-250                    |
| CONNECTIONS                 |                            |
| Side A - Connector 1        | BS1363 UK PLUG             |
| Side B - Connector 1        | IEC-320-C5                 |
| PHYSICAL                    |                            |

### Highlights

- UK computer power cable for powering notebooks and laptops with C6 inlets
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing UK IEC power cord

### Applications

- Connect a laptop or notebook computer to a PDU up to 6 ft. (1.8 m) away in your workstation
- Extend an existing power connection up to 6 ft. (1.8 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P060-006 BS1363 to C5 UK Computer Power Cable, 6 ft. (1.8 m), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                                |
|--------------------------------------|--------------------------------|
| Plug Color                           | Black                          |
| Cable Jacket Color                   | Black                          |
| Cable Jacket Material                | PVC                            |
| Power Cord Jacket Type               | H05VV-F                        |
| Cable Outer Diameter (OD)            | 6.5mm                          |
| Number of Conductors                 | 3                              |
| Wire Gauge (AWG)                     | 18                             |
| Wire Gauge (OD - mm <sup>2</sup> )   | 0.82                           |
| Cable Length (ft.)                   | 6                              |
| Cable Length (m)                     | 1.83                           |
| Shipping Dimensions (hwd / in.)      | 9.06 x 7.09 x 0.50             |
| Shipping Dimensions (hwd / cm)       | 23.01 x 18.01 x 1.27           |
| Shipping Weight (lbs.)               | 0.46                           |
| Shipping Weight (kg)                 | 0.21                           |
| Unit Dimensions (hwd / in.)          | 9.060 x 7.090 x 0.500          |
| <b>ENVIRONMENTAL</b>                 |                                |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C)    |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C)    |
| Operating Humidity Range             | 20% to 70% RH                  |
| Storage Humidity Range               | 20% to 80% RH                  |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                |
| Antibacterial                        | No                             |
| Angled Plug                          | No                             |
| High Voltage                         | Yes                            |
| Locking Plug                         | No                             |
| Coiled Power Cord                    | No                             |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                |
| Product Certifications               | UL Listed; cUL Listed          |
| Product Compliance                   | CE (Europe); REACH; RoHS; UKCA |
| <b>WARRANTY &amp; SUPPORT</b>        |                                |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty      |



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.