

Keyspan Mini DisplayPort to Active VGA Adapter, Video Converter, DP1.2, (M/F), White, 6-in. (15.24 cm)

MODEL NUMBER: **P137-06N-VGA-V2**



Highlights

- Connect a VGA monitor to a computer with a Mini-DisplayPort or Thunderbolt 1/2 output
- Mini-DisplayPort v1.2 to VGA Active Adapter Converter (Mini-DisplayPort Male to VGA Female)
- Plug-and-play convenience; no drivers or software needed
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

Package Includes

- Mini-DisplayPort 1.2 to VGA Active Adapter Converter (Mini-DP Male to VGA Female) 6-in.

Features

- Connect a VGA monitor to a computer with a Mini-DisplayPort or Thunderbolt 1/2 output
- Mini-DisplayPort v1.2 to VGA Active Adapter Converter (Mini-DisplayPort Male to VGA Female)
- Supports VGA computer video resolutions up to 1920 x 1200 and HD resolutions up to 1080p
- 17.28 Gbps bandwidth
- Plug and Play; no drivers or software require
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

Specifications

OVERVIEW	
UPC Code	037332187543
Product Type	Video Adapter
Technology	VGA/SVGA; DisplayPort
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
PHYSICAL	
Color	White
Cable Length (ft.)	0.5



Powering Business Worldwide



Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.