

## Keyspan Mini DisplayPort to DisplayPort Compact Adapter and Video Converter (M/F)

MODEL NUMBER: P139-000-DP



Connects a computer with a Mini DisplayPort (mDP) output to a high-definition monitor, projector or television with a DisplayPort™ input. Recommended for use with Microsoft Surface.

### Description

The P139-000-DP Keyspan® Mini DisplayPort to DisplayPort Compact Adapter and Video Converter (M/F) connects your existing mDP device to a high-definition DisplayPort monitor, projector or television. By converting the mDP connector to DisplayPort, the P139-000-DP allows you to continue using your existing DisplayPort display instead of buying a new Mini DisplayPort monitor. Recommended for laptops, tablets and Microsoft Surface devices, the P139-000-DP is ideal for displaying crystal-clear video on a large monitor or digital sign. It supports high-definition video resolutions up to 1920 x 1200, including 1080p, at 60 Hz. The compact one-piece molded adapter is designed to go where you go. It fits into your pocket, purse, or laptop bag, allowing you to quickly connect your computer to a DisplayPort display using your regular DisplayPort cable. Compliant with HDCP 2.2 and DisplayPort 1.2. Plug-and-play design requires no software or drivers.

### Features

#### Sends Mini DisplayPort Audio/Video to a DisplayPort Display

- Connects an mDP computer to a DisplayPort monitor, projector or TV
- Ideal for displaying Mini DisplayPort video on a large monitor or digital sign
- Allows you to continue using an existing DisplayPort display, instead of buying a new monitor
- Recommended for laptops, tablets and Microsoft Surface devices

#### Vibrant Video Quality

- Supports HD video resolutions up to 1920 x 1200, including 1080p, @ 60 Hz
- Compliant with HDCP 2.2 and DisplayPort 1.2

#### Superior Design for Superior Performance

- Compact 1-piece molded design easy to carry in pocket or purse for quick connection anywhere
- Plug and play—no software or drivers required

### Highlights

- Supports HD video resolutions up to 1920 x 1200 @ 60 Hz
- Compliant with HDCP 2.2 and DisplayPort 1.2
- Compact 1-piece molded design is easy to carry
- Ideal for laptops, tablets and Microsoft Surface devices
- Plug and play—no software or drivers required

### System Requirements

- Source device with Mini DisplayPort connector
- Display device with DisplayPort connector

### Package Includes

- P139-000-DP Keyspan Mini DisplayPort to DisplayPort Compact Adapter and Video Converter (M/F)

## Specifications

OVERVIEW	
UPC Code	037332205773
Technology	DisplayPort
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Weight (lbs.)	0.02
Shipping Weight (kg)	0.01
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	5 to 122 F (-15 to 50 C)
Relative Humidity	0% TO 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
FEATURES & SPECIFICATIONS	
HDCP Specification	2.2
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty