

Keyspan Mini DisplayPort to DisplayPort Compact Adapter and Video Converter (M/F)

MODEL NUMBER: P139-000-DP



Connects a computer with a Mini DisplayPort (mDP) output to a high-definition monitor, projector or television with a DisplayPort™ input. Recommended for use with Microsoft Surface.

Description

The P139-000-DP Keyspan® Mini DisplayPort to DisplayPort Compact Adapter and Video Converter (M/F) connects your existing mDP device to a high-definition DisplayPort monitor, projector or television. By converting the mDP connector to DisplayPort, the P139-000-DP allows you to continue using your existing DisplayPort display instead of buying a new Mini DisplayPort monitor.

Recommended for laptops, tablets and Microsoft Surface devices, the P139-000-DP is ideal for displaying crystal-clear video on a large monitor or digital sign. It supports high-definition video resolutions up to 1920 x 1200, including 1080p, at 60 Hz. The compact one-piece molded adapter is designed to go where you go. It fits into your pocket, purse, or laptop bag, allowing you to quickly connect your computer to a DisplayPort display using your regular DisplayPort cable.

Compliant with HDCP 2.2 and DisplayPort 1.2. Plug-and-play design requires no software or drivers.

Features

Sends Mini DisplayPort Audio/Video to a DisplayPort Display

- Connects an mDP computer to a DisplayPort monitor, projector or TV
- Ideal for displaying Mini DisplayPort video on a large monitor or digital sign
- Allows you to continue using an existing DisplayPort display, instead of buying a new monitor
- Recommended for laptops, tablets and Microsoft Surface devices

Vibrant Video Quality

- Supports HD video resolutions up to 1920 x 1200, including 1080p, @ 60 Hz
- Compliant with HDCP 2.2 and DisplayPort 1.2

Superior Design for Superior Performance

- Compact 1-piece molded design easy to carry in pocket or purse for quick connection anywhere
- Plug and play—no software or drivers required

Specifications

Highlights

- Supports HD video resolutions up to 1920 x 1200 @ 60 Hz
- Compliant with HDCP 2.2 and DisplayPort 1.2
- Compact 1-piece molded design is easy to carry
- Ideal for laptops, tablets and Microsoft Surface devices
- Plug and play—no software or drivers required

System Requirements

- Source device with Mini DisplayPort connector
- Display device with DisplayPort connector

Package Includes

- P139-000-DP Keyspan Mini DisplayPort to DisplayPort Compact Adapter and Video Converter (M/F)



Powering Business Worldwide



OVERVIEW	
UPC Code	037332205773
Product Type	Video Adapter
Technology	DisplayPort
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Weight (lbs.)	0.02
Shipping Weight (kg)	0.01
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0% TO 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
HDCP Specification	2.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.