

The P130-000-COMP is intended for applications such as viewing video content with audio. For standard computer usage, desktop icons and other text may appear less sharp than if a direct cable connection is used.

HDMI to RCA Composite Video with Audio Converter (HDMI Female/3x RCA Female)

MODEL NUMBER: P130-000-COMP



Convert an HDMI audio/video signal for use with an analog TV or monitor equipped with RCA composite video and audio ports.

Features

Convert HDMI to Composite Video and Audio for Compatibility with Analog Displays Tripp Lite's P130-000-COMP converter enables connection of an HDMI source, such as a laptop or Blu-ray player, to a television, monitor or projector equipped with RCA composite audio/video connectors. A switch allows you to select either the NTSC or PAL video standard for compatibility with a wide range of devices. The converter has a female HDMI input and female RCA composite video (yellow) and stereo audio (red and white) outputs; cables are sold separately.

Save Money without Sacrificing Image and Sound Quality

This HDMI to composite video and audio converter helps you save money by making your current composite video television or monitor compatible with an HDMI-equipped video source, eliminating the need to purchase a new HDMI display. It is HDCP compliant and supports HDMI input video resolutions of 480i, 480p, 576i, 576p, 720p, 1080i and 1080p (50/60 Hz). The converter supports output video resolutions up to 480i (NTSC) and 576i (PAL). It also supports uncompressed two-channel (right/left) stereo audio.

Simplify Installation with a Versatile Plug-and-Play Solution Entirely plug and play, this converter does not require software or drivers. Just connect your devices and plug in the included 100-240V power supply. Suitable for use in many countries, the power supply comes with four plug adapters: NEMA 1-15P (North America), CEE 7/16 Schuko (Europe), BS1363 (United Kingdom) and AS/NZS 3112 (Australia).

2-Year Warranty The P130-000-COMP is backed by a 2-year warranty, ensuring reliability and performance.

Highlights

- Allows an HDMI video source to work with RCA A/V ports
- Converts high-quality HDMI video up to 1080p
- Supports both NTSC (up to 480i) and PAL (up to 576i) video standards
- 100-240V power supply and plug adapters offer wide compatibility
- Plug and play; does not require software or drivers

Applications

- View video from a laptop or Blu-ray player on a display equipped with RCA composite video and audio ports
- Continue to use a composite video display instead of purchasing a new HDMI-enabled display

System Requirements

- Video source with HDMI output
- Display with RCA composite video and stereo audio inputs

Package Includes

- P130-000-COMP HDMI to Composite Video with Audio Converter (F/3xF)
- External power supply (Input: 100-240V, 50/60 Hz, 0.3A; Output: 5V, 1A) with 5 ft. cord
- Plug adapters (North America, Europe, United Kingdom and Australia)
- Mounting hardware



- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332192738
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	5.08 x 18.80 x 21.59
Shipping Dimensions (hwd / in.)	2.00 x 7.40 x 8.50
Shipping Weight (kg)	0.54
Shipping Weight (lbs.)	1.20
Unit Dimensions (hwd / in.)	0.98 x 4.02 x 3.94
Unit Weight (kg)	0.62
Unit Weight (lbs.)	1.36
FEATURES & SPECIFICATIONS	
Technology	Composite; HDMI; Stereo Audio
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>