

HDMI/DVI to DisplayPort Active Converter, HDMI to DisplayPort (F/F), 1920 x 1200 (1080p)

MODEL NUMBER: P130-000-DP



Converts an HDMI audio/video signal for display on a DisplayPort monitor. Also converts DVI and mini-DVI video signals using adapter cables (sold separately). Ideal for video game consoles and home theaters.

Description

The P130-000-DP HDMI/DVI to DisplayPort Active Converter connects an HDMI source, such as a computer or Blu-ray™ player, to a DisplayPort or Mini DisplayPort monitor. With a female HDMI input port and a female DisplayPort output port, this converter lets you use your existing DisplayPort display instead of buying a new HDMI monitor or television. It also connects DVI or mini-DVI sources to a DisplayPort monitor using adapter cables (sold separately), such as Tripp Lite's P566-Series DVI to HDMI cables.

Ideal for video graphics cards, video game consoles or home theater receivers, the P130-000-DP supports video resolutions up to 1920 x 1200, including 1080p. It also supports HDMI uncompressed two-channel audio, such as LPCM, and it's compliant with HDCP (High-Definition Content Protection). Stores EDID information to ensure top display compatibility. Installation is quick and simple, with no software or drivers to install. Locate your HDMI source up to 5m (16ft) from the Active Converter and the Active Converter up to 3m (10ft) from a display. Fits easily in a briefcase, backpack or laptop bag for connecting on the go. HDMI and DisplayPort cables sold separately.

Features

Sends HDMI Audio/Video Signals to a DisplayPort Monitor

- Ideal for video graphics cards, video game consoles or home theater receivers
- Connects HDMI source to DisplayPort display
- Connects DVI or mini-DVI source using adapter cables, such as Tripp Lite's P566-Series (sold separately)
- Female HDMI and DisplayPort connectors
- Fits easily into briefcase, backpack or laptop bag
- Plug-and-play—no software or drivers necessary

Vibrant Audio/Video Quality

Highlights

- Active converter works with all HDMI sources
- Supports video resolutions up to 1920 x 1200, including 1080p
- Supports HDMI uncompressed 2-channel audio, including LPCM
- Stores EDID info to ensure optimal display compatibility
- Compliant with HDCP

System Requirements

- Computer or Blu-ray player with HDMI port
- Monitor with DisplayPort
- DisplayPort cable being used must not exceed 3m (10ft)
- HDMI cable being used must not exceed 5m (16ft)

Package Includes

- P130-000-DP HDMI/DVI to DisplayPort Active Converter
- External power supply with NEMA 1-15P plug and 3.5 ft. cord (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V, 2A)
- Owner's manual



- Supports video resolutions up to 1920 x 1200, including 1080p
- Supports HDMI uncompressed 2-channel audio, including LPCM
- Complies with HDCP
- Stores EDID information to ensure optimal display compatibility

Specifications

OVERVIEW	
UPC Code	037332192721
Technology	DVI; HDMI; DisplayPort
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	7.62 x 13.21 x 18.03
Shipping Dimensions (hwd / in.)	3.00 x 5.20 x 7.10
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>