

DisplayPort to DVI Cable Adapter, Converter for DP-M to DVI-I-F, 6 in., 50 Pack

MODEL NUMBER: **P134-000-50BK**



Passive adapters connect your computer or tablet's DisplayPort™ to the DVI input on a monitor, projector or television. Source devices must have DisplayPort++ (DP++) for HDMI/DVI pass-through.

Description

The P134-000-50BK is a bulk pack of fifty (50) P134-000 DisplayPort to DVI Cable Adapters (M/F). Each adapter connects a DisplayPort computer or tablet to the DVI input port on a monitor, projector or television. With a male DisplayPort connector and a female DVI-I dual-link connector, each adapter lets you use your existing DVI display instead of buying a new DisplayPort monitor.

Ideal for displaying video on a large monitor or digital sign, these six-inch adapters support DVI-D single-link computer video resolutions up to 1920 x 1200 and HD video resolutions up to 1920 x 1080 (1080p). Because they are passive adapters, these units require that the connected source device have a DP++ port, which allows HDMI and DVI signals to pass through (check your DisplayPort source's documentation for compatibility).

Foil and braid shielding delivers reliable, error-free signal quality and helps protect from EMI/RFI line noise that can distort or destroy data. Fully molded ends with corrosion-resistant gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

These P134-000 adapters are plug-and-play units with no software, drivers or power supply needed. They fit easily in a briefcase, backpack or laptop bag for connecting on the go.

Features

Send High-Definition DisplayPort Video Signals to a DVI Display

- Connects DisplayPort computer or tablet to DVI-enabled monitor, projector or TV
- Recommended for digital signage or presentations in a classroom or conference room

Highlights

- 50-piece bulk pack of P134-000 DisplayPort to DVI adapters
- Supports DVI-D single-link video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1080p
- Premium foil and braid shielding helps protect against EMI/RFI noise
- Plug and play—no software, drivers or power supply needed

System Requirements

- Source device with DisplayPort output
- Display device with DVI input
- Source must have DP++ port for HDMI/DVI pass-through
- Not for use with MST hubs

Package Includes

- (50) P134-000 DisplayPort to DVI Cable Adapters (M/F), 6 in.



- Male DisplayPort and female DVI-I dual-link connectors
- Bulk pack includes 50 Tripp Lite P134-000 DisplayPort to DVI converters

Vibrant Video Quality

- Supports DVI-D single-link video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Passive adapter requires source device to have DP++ compatibility for HDMI/DVI signal pass-through

Superior Materials for Superior Performance

- Foil and braid shielding helps protect against EMI/RFI line noise that can distort or destroy data
- Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking

Convenient to Use Anywhere

- Plug-and-play—no software, drivers or power supply necessary
- Fits easily into briefcase, backpack or laptop bag

Specifications

OVERVIEW	
UPC Code	037332205506
Technology	DVI; DisplayPort
INPUT	
Cable Length (ft.)	0.5
Cable Length (in.)	6
Cable Length (cm)	15.24
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	16.08 x 30.18 x 17.14
Shipping Dimensions (hwd / in.)	6.33 x 11.88 x 6.75
Shipping Weight (kg)	2.72
Shipping Weight (lbs.)	6.00
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>