

DisplayPort to DVI Cable Adapter, Converter for DP-M to DVI-I-F, 6-in. (15.24 cm), 50 Pack

MODEL NUMBER: P134-000-50BK



Passive adapters connect your computer or tablet's DisplayPort™ to the DVI input on a monitor, projector or television. Source devices must have DisplayPort++ (DP++) for HDMI/DVI pass-through.

Features

Send High-Definition DisplayPort Video Signals to a DVI Display

- Connects DisplayPort computer or tablet to DVI-enabled monitor, projector or TV
- Recommended for digital signage or presentations in a classroom or conference room
- Male DisplayPort and female DVI-I dual-link connectors
- Connect to any Displayport 1.1/1.2/1.4/2.1 version graphics card with Dual Mode DP++ (DisplayPort ++) port, which allows HDMI and DVI signals to be passed through; check the documentation for your DisplayPort source for compatibility.
- Bulk pack includes 50 P134-000 DisplayPort to DVI converters

Vibrant Video Quality

- Supports DVI-D single-link video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Passive adapter requires source device to have DP++ compatibility for HDMI/DVI signal pass-through

Superior Materials for Superior Performance

- Foil and braid shielding helps protect against EMI/RFI line noise that can distort or destroy data
- Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking

Convenient to Use Anywhere

- Plug-and-play—no software, drivers or power supply necessary
- Fits easily into briefcase, backpack or laptop bag

Specifications

OVERVIEW

Highlights

- Connect a DVI monitor to a computer with a DisplayPort output
- Adapter cable connects DVI monitor to any DisplayPort 1.1/1.2/1.4/2.1 version dual-mode port
- DisplayPort to DVI Adapter Converter (DisplayPort-Male to DVI-I-Female), 6 in.
- Plug-and-play convenience; no drivers or software needed
- Supports DVI-D single-link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port
- HDCP 1.x or 2.x version & DDC pass-through ensure compatibility between source & display

System Requirements

- Source device with DisplayPort output
- Display device with DVI input
- Source must have DP++ port for HDMI/DVI pass-through
- Not for use with MST hubs

Package Includes

- (50) P134-000 DisplayPort to DVI Cable Adapters (M/F), 6 in.



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332205506
Product Type	Video Adapter
Device Compatibility	Computer; DVR; Laptop; Monitor/HDTV; Projector; Server
Technology	DVI; DisplayPort
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	6.33 x 11.88 x 6.75
Shipping Dimensions (hwd / cm)	16.08 x 30.18 x 17.14
Shipping Weight (lbs.)	6.00
Shipping Weight (kg)	2.72
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	16.08 x 30.18 x 17.14
Unit Weight (lbs.)	6.0
Unit Weight (kg)	2.72
STANDARDS & COMPLIANCE	
Product Certifications	2MOPP
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.