

DisplayPort to DVI Active Adapter Video Converter (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P134-06N-DVIACT



Converts a Single-Mode DisplayPort signal for use with a DVI-D monitor, display or projector

Features

- Active adapter cable for use with any Displayport port
- Converts a Single-Mode DisplayPort signal for use with a DVI-D monitor, display or projector
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output
- Supports computer video resolutions up to 1920 x 1200, and HD video resolutions up to 1080p
- Displayport 1.1a compliant
- Plug and Play...no software or drivers
- No external power required

Specifications

OVERVIEW	
UPC Code	037332185310
Technology	DVI; DisplayPort
PHYSICAL	
Color	Black
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	12.19 x 13.46 x 4.06
Shipping Dimensions (hwd / in.)	4.80 x 5.30 x 1.60

Highlights

- Active adapter cable for use with any Displayport port
- Connect a DVI-D monitor, display or projector to a computer with a DisplayPort output
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output
- Supports computer video resolutions up to 1920 x 1200, and HD video resolutions up to 1080p

System Requirements

- Computer with DisplayPort output
- Monitor, display or projector with a DVI input
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P134-06N-DVI-V2

Package Includes

- P134-06N-DVIACT DisplayPort to DVI Active Converter (M/F), 6 in.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	0.12
Shipping Weight (lbs.)	0.26
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>