

DisplayPort to VGA/DVI/HDMI All-in-One Converter Adapter - 4K 60 Hz HDMI, DP 1.2

MODEL NUMBER: **P136-06N-HDV4K6**



All-in-one converter/adapter connects your DisplayPort-enabled laptop or tablet to a VGA, DVI or HDMI display without the need to carry separate adapters.

Description

No more carrying around separate adapters for various monitors, projectors and televisions. The P136-06N-HDV4K6 DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter connects your laptop or tablet's DisplayPort to a VGA, DVI or HDMI display. The simple all-in-one solution for displaying content on a larger screen, the P136-06N-HDV4K6 is ideal for trade shows, classrooms, lecture halls and anywhere else you might give a presentation.

The all-in-one unit contains separate female DVI, HD15 and HDMI ports. It supports video resolutions up to 1920 x 1080, including 1080p (DVI); 1920 x 1200, including 1080p (HD15); and 4K x 2K (HDMI) at 60 Hz, as specified in HDMI 2.0. It also supports 36-bit Deep Color (12 bits per channel). This adapter supports HDCP 2.2.

The P136-06N-HDV4K6 is compatible with laptops, tablets and other devices equipped with a female DisplayPort. It's completely plug-and-play with no software, drivers or external power supply needed. With its small size and built-in cable, the P136-06N-HDV4K6 is recommended for stowing in your laptop bag and carrying to school, the office or the latest trade show.

Features

Connects Your DisplayPort Laptop or Tablet to a VGA, DVI or HDMI Display Recommended for trade shows, classrooms, lecture halls and other presentation venues
 DVI port supports video resolutions up to 1920 x 1080 (1080p)
 HD15 port supports video resolutions up to 1920 x 1200, including 1080p
 HDMI port supports video resolutions up to 4K x 2K (3840 x 2160) @ 60 Hz, as specified in HDMI 2.0
 Supports 36-bit Deep Color (12 bits per channel)
 Supports HDCP 2.2

Plug-and-Play Convenience No software, drivers or external power supply required
 Small enough to stow in laptop bag or briefcase

Highlights

- Separate DVI, HD15 and HDMI female connectors
- Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Supports HDCP 2.2
- Plug-and-play operation with no software required for easy, immediate installation
- Small size for easy carrying in laptop bag or briefcase

System Requirements

- Computer or tablet with DisplayPort output
- Display device with VGA, DVI or HDMI input

Package Includes

- P136-06N-HDV4K6 DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter, 6 in.
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332202741



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Technology	DVI; HDMI; VGA/SVGA; DisplayPort
PHYSICAL	
Color	Black
Cable Length (in.)	6
Shipping Dimensions (hwd / cm)	2.29 x 9.91 x 14.22
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.60
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
FEATURES & SPECIFICATIONS	
HDCP Specification	2.2
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>