

Keyspan Mini DisplayPort to VGA/DVI/HDMI All-in-One Video Converter Adapter, 4K 60 Hz HDMI, DP 1.2, Black, 6 in.

MODEL NUMBER: P137-06N-HDVK6B



Mini DP to HDMI/VGA/DVI adapter connects your Mini DP or Thunderbolt 1/2 laptop to a VGA, DVI or HDMI display.

Features

Converter Connects a Mini DisplayPort Device to a VGA, DVI or HDMI Display

No more carrying around separate adapters for various monitors, projectors and televisions. This Keyspan® Mini DP to HDMI/VGA/DVI adapter connects a VGA, DVI or HDMI display to the Mini DisplayPort or Thunderbolt 1 or 2 port on your Chromebook, MacBook, Microsoft Surface or other compatible laptop or tablet. Only one display can be connected at a time.

Simple All-in-One Solution for Displaying 4K Video on a Large Screen

The P137-06N-HDVK6B is ideal for classrooms, lecture halls and anywhere else you may need to connect to a monitor. Just connect the converter between your laptop and a VGA, DVI or HDMI display. You no longer have to dig around in your laptop bag for the correct adapter.

Transmits Crystal-Clear Video up to 4K x 2K for Ultra HD Presentations

This all-in-one unit features separate female HD15, DVI and HDMI ports. The HD15 port supports high-definition video resolutions up to 1920 x 1200, including 1080p. The DVI-D single-link port supports HD resolutions up to 1920 x 1080 (1080p). The HDMI port supports Ultra HD 4K x 2K video (3840 x 2160) at 60 Hz, as specified in HDMI 2.0, as well as 36-bit Deep Color (12 bits per channel), and HDCP 2.2. The HDMI port is backward compatible with non-4K displays.

Ready to Use Right from the Package, So You Can Plug and Play Immediately

The plug-and-play Mini DP to HDMI adapter requires no software, drivers or external power, works with both Windows and Mac operating systems, and is compatible with laptops, tablets and other devices equipped with a female Mini DisplayPort or Thunderbolt 1 or 2 port. With its small size and built-in cable, the P137-06N-HDVK6B is recommended for stowing in your laptop bag and carrying to school or the office.

3-Year Warranty

The P137-06N-HDVK6B is backed by a 3-year warranty, ensuring reliability and performance.

Specifications

OVERVIEW	
UPC Code	037332210647
Product Type	Video Adapter

Highlights

- Multiple video outputs connect to most displays—no more carrying multiple adapters
- HDMI port delivers UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- DVI and VGA ports support 1080p for sharp HD video presentations
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect your laptop to a VGA, DVI or HDMI monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the PC or laptop in your office or home workspace

System Requirements

Package Includes

- P137-06N-HDVK6B Keyspan Mini DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter, Black
- Owner's manual



Powering Business Worldwide



Technology	DVI; HDMI; VGA/SVGA; DisplayPort
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
PHYSICAL	
Color	Black
Cable Length (in.)	6
Shipping Dimensions (hwd / in.)	0.91 x 5.40 x 3.90
Shipping Dimensions (hwd / cm)	2.31 x 13.72 x 9.91
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
FEATURES & SPECIFICATIONS	
HDCP Specification	2.2
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.