

3.5 mm Mini Stereo to RCA Audio Y Splitter Adapter Cable (M/2xM), 6 ft. (1.8 m)

MODEL NUMBER: P314-006



Highlights

- Audio Cable Y Adapter 3.5mm-M/(2) RCA-M - 6 ft.
- Connect a device with a 3.5 mm jack to a sound system with RCA inputs or a sound system with RCA inputs to a device with a 3.5 mm jack
- Perfect for your PC, notebook, MP3 player or iPod
- Molded cable with built-in strain relief

Package Includes

Audio Y Splitter Adapter 3.5MM Plug/2 RCA Plugs, 6 ft. (1.8 m)

Description

Six-foot (1.8 meters) audio Y splitter/adapter cable. This cable has a 3.5 mm plug on one end and two RCA plugs on the other. Enables a PC sound card, portable CD player, MP3 player, iPod or any other audio device with a 3.5 mm mini-stereo jack to connect to an audio device with RCA audio inputs or an audio device with RCA audio inputs to connect to a PC sound card, portable CD player, MP3 player, iPod or any audio device with 3.5 mm mini-stereo jack.

Features

- Molded cables with built-in strain relief
- 3.5mm (male) to (2x) RCA (male)

Specifications

OVERVIEW	
UPC Code	037332012142
Product Type	Passive Cable
Technology	Stereo Audio
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	3.5MM (MALE)
Side B - Connector 1	(2) RCA (MALE)
Latching or Gripping Connector	No
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	6
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://triplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.