

DVI Y Splitter Cable, Digital Monitors (DVI-D M to 2x F), 1 ft.

MODEL NUMBER: **P564-001**



Description

Tripp Lite's 1 ft. DVI Splitter cable provides an inexpensive alternative for splitting the video signal from your PC's DVI port to two DVI enabled monitors. Supports video resolutions up to 1920 x 1080. The P564-001 is designed for two DVI-D monitors to be connected at the same time. If only one monitor is connected, and the other DVI-D Female port left open, video quality will be negatively affected.

Features

- DVI-D Male to 2 x DVI-D Female, 1 ft.
- Inexpensive solution for presentations
- Supports video resolutions up to 1920 x 1080
- Molded, double-shielded construction for maximum EMI/RFI protection
- Two monitors display the same image from one PC
- The P564-001 is designed for two DVI-D monitors to be connected at the same time. If only one monitor is connected, and the other DVI-D Female port left open, video quality will be negatively affected

Specifications

OVERVIEW	
UPC Code	037332138798
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.3

Highlights

- Splits the digital (DVI) signal providing simultaneous display of the same image on two DVI monitors
- DVI-D male splits to two (2) DVI-D females
- Supports video resolutions up to 1920 x 1080

System Requirements

- DVI-D or DVI-I Female PC Card Connector, and DVI Enabled Monitors
- The P564-001 is designed for two DVI-D monitors to be connected at the same time. If only one monitor is connected, and the other DVI-D Female port left open, video quality will be negatively affected

Package Includes

- DVI-D Male to (2) DVI-D Female Cable - 1 ft.



PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.10
Shipping Weight (lbs.)	0.22
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 1	(2) DVI-D DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
FEATURES & SPECIFICATIONS	
Technology	DVI
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>