

## VGA Easy Pull High-Resolution RGB Coaxial Cable (HD15 M/M), 100 ft.

MODEL NUMBER: P503-100



### Highlights

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection

### Package Includes

- 100 ft. Male/Male Easy Pull SVGA/VGA Monitor Cable w/ Connectors

### Description

Tripp Lite's 100 ft. SVGA/VGA Easy Pull Monitor Cable with Connectors makes running long length video cables a snap. The pull-apart design allows the cable to be run through conduit or other tight areas that a HD15 connector wouldn't fit through. Diameter of the circular DIN end is only 7/8". Circular Easy Pull connector is threaded to ensure maximum security once the cable is reattached. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 males are molded and have integral strain relief to ensure they last a long time.

### Features

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- RGB 75-ohm coax construction for maximum video resolution
- HD15 male to HD15 male molded connectors
- Supports resolutions up to 1600 x 1200

## Specifications

OVERVIEW	
UPC Code	037332142276
Technology	Coax; VGA/SVGA
INPUT	
Cable Length (ft.)	100



Cable Length (m)	30.5
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 2.54
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 1.00
Shipping Weight (kg)	3.45
Shipping Weight (lbs.)	7.60
<b>CONNECTIONS</b>	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (MALE)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS-Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>