

HDMI to DVI Adapter Cable (M/M), 50 ft. (15.2 m)

MODEL NUMBER: **P566-050**



Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and DVI-enabled display.

Description

Tripp Lite's 50-ft. (15.24 m) DVI - HDMI (High Definition Multimedia Interface) cable allows interconnection between digital display devices, such as DTV's (Digital Television), Plasma displays, LCD TV's, and projectors, to Digital source devices, such as Digital Set-Top boxes, DVD/DVD-R players, and AV receivers. HDMI DTV's will display video received from existing DVI-equipped products, and DVI-equipped TVs will display video from HDMI sources. The DVI-HDMI adapter does not support audio.

Features

- 50-ft. (15.24 m) HDMI to DVI-D Single Link Adapter Cable
- Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and a DVI-enabled display.
- Gold plated connectors and contacts provide optimal signal transfer
- Premium Double-Shielded HDMI compliant cable protects against outside noise (EMI/RFI)
- Impedance matched twisted pair construction reduces cross-talk and interference
- Supports High-Definition (HD) video resolutions up to 1920 x 1080 @60Hz (1080p).

Specifications

| OVERVIEW | |
|------------|--------------|
| UPC Code | 037332181336 |
| Technology | DVI; HDMI |
| Cable Type | Passive |
| PHYSICAL | |
| Color | Black |

Highlights

- Premium double shielded digital video cable protects against EMI/RFI noise.
- Gold plated connectors and contacts provide optimal signal transfer.
- Supports high-def video resolutions up to 1920 x 1080 @60Hz (1080p).
- Supports a bandwidth up to 5Gbps
- This product is covered by a Lifetime Limited Warranty

Package Includes

- 50-ft. (15.24 m) HDMI to DVI Gold Digital Video Cable - HDMI-M/DVI-M

| | |
|--------------------------------------|---------------------------|
| Cable Jacket Color | Black |
| Cable Length (ft.) | 50 |
| Cable Length (m) | 15.24 |
| Shipping Dimensions (hwd / in.) | 1.50 x 6.80 x 7.80 |
| Shipping Dimensions (hwd / cm) | 3.81 x 17.27 x 19.81 |
| Shipping Weight (lbs.) | 1.80 |
| Shipping Weight (kg) | 0.82 |
| CONNECTIONS | |
| Side A - Connector 1 | HDMI (MALE) |
| Side B - Connector 1 | DVI-D SINGLE LINK (MALE) |
| Latching or Gripping Connector | No |
| FEATURES & SPECIFICATIONS | |
| IP68 Rated | No |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |