

## HDMI to VGA + Audio Active Adapter Cable (HDMI to Low-Profile HD15 + 3.5 mm M/M), 6 ft. (1.8 m)

MODEL NUMBER: **P566-006-VGA-A**



Converts an HDMI audio/video signal for presentation on an existing VGA monitor, projector or television and 3.5 mm mini stereo speakers, saving you the time, effort and expense of upgrading to a new HDMI display.

### Features

#### Send High-Definition HDMI Audio/Video Signals to a VGA Display

- Connects HDMI source to a VGA monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Low-profile HD15 connector fits neatly into tight spaces
- Attached 3.5 mm plug allows connection of compatible mini stereo speakers
- Plug-and-play—no software or drivers necessary

#### Vibrant, Superior Video Quality

- Supports HD video resolutions up to 1920 x 1200 @ 60 Hz

#### Superior Materials for Superior Performance

- Foil and braid shielding for reliable protection from EMI/RFI line noise
- Gold-plated HDMI connector and contacts for maximum conductivity and minimum data loss
- Integral strain relief reduces stress and adds flexibility
- Impedance-matched twisted-pair construction reduces crosstalk and interference
- USB Micro-B port provided in case additional power is needed

## Specifications

### OVERVIEW

### Highlights

- Supports HD video resolutions up to 1920 x 1200 @ 60 Hz
- Gold-plated HDMI connector for maximum conductivity
- Foil and braid shielding for reliable EMI/RFI line noise protection
- Low-profile VGA connector fits neatly into tight spaces
- Plug-and-play with no software or drivers required

### System Requirements

- Computer or other source with HDMI female connector
- Monitor or other display with VGA female connector
- USB Micro-B to A cable and USB power source (only if additional power is needed)

### Package Includes

- P566-006-VGA-A HDMI to VGA + Audio Active Converter Cable, 6 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

UPC Code	037332201041
Product Type	Active
Technology	HDMI; VGA/SVGA
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
<b>CONNECTIONS</b>	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HD15 (MALE) - LOW PROFILE
Side B - Connector 2	3.5MM (MALE)
Side B - Connector 3	MICRO-USB B (FEMALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>