

HDMI to DVI Adapter Cable (M/M), 12 ft. (3.7 m)

MODEL NUMBER: P566-012



Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and DVI-enabled display.

Description

This DVI - HDMI cable allows interconnection between digital display devices, including HDTVs and projectors, to digital source devices, such as satellite/cable boxes, Blu-ray players and AV receivers. HDMI DTVs will display video received from existing DVI-equipped products, and DVI-equipped TVs will display video from HDMI sources. HDMI technology uses a much more compact and user-friendly connector than the existing DVI connector. The HDMI specification handles higher bandwidth, uncompressed video and multi-channel digital audio, all in one neat cable solution. (DVI-HDMI cable supports digital video only).

Features

- 12-ft. (3.66 m) DVI to HDMI Adapter Cable
- Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and a DVI-enabled display.
- Gold plated connectors and contacts provide optimal signal transfer
- Premium Double-Shielded HDMI compliant cable protects against outside noise (EMI/RFI)
- Impedance matched twisted pair construction reduces cross-talk and interference
- Supports High-Definition (HD) video resolutions up to 1920 x 1080 @60Hz (1080p).

Specifications

OVERVIEW	
UPC Code	037332181329
Product Type	Passive Cable
Technology	DVI; HDMI
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)

Highlights

- Premium double shielded digital video cable protects against EMI/RFI noise
- Gold plated connectors and contacts provide optimal signal transfer
- Supports high-def video resolutions up to 1920 x 1080 @ 60 Hz (1080p)
- Supports a bandwidth up to 5 Gbps

Package Includes

- 12-ft. (3.66 m) HDMI to DVI Gold Digital Video Cable (HDMI-M / DVI-M)



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Length (ft.)	12
Cable Length (m)	3.66
Cable Length (in.)	144
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.55
Shipping Weight (kg)	0.25
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.