

DisplayPort 1.2 to HDMI Active Adapter Cable, Gripping HDMI Plug, HDCP 2.2, 4K @ 60 Hz (M/M), 3 ft. (0.91 m)

MODEL NUMBER: P582-003-HD-V2A



Highlights

- Supports video resolutions up to 4K @ 60 Hz (3840 x 2160), as specified in HDMI 2.0
- Compliant with latest HDCP 2.2 standards
- No separate power adapter required
- High-grip HDMI plug prevents accidental disconnections

Package Includes

- P582-003-HD-V2A DisplayPort 1.2a to HDMI Active Adapter Cable (M/M), 3 ft.

HDCP 2.2-compliant cable connects the DisplayPort™ output on your PC or Mac to a 4K-enabled HDMI monitor, projector or television.

Features

Send UHD DisplayPort 1.2a Signals to a 4K HDMI Display Connects DisplayPort PC or Mac to a 4K-enabled HDMI monitor, projector or HDTV. Recommended for displaying video on a large monitor or digital sign. DisplayPort and high-grip HDMI male connectors. No separate power adapter required.

Vibrant Video Quality Supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160), as specified in HDMI 2.0. Supports HDCP 2.2, audio and EDID. Active adapter compatible with Single-Mode and Dual-Mode (DP++) DisplayPort output. Recommended for graphics cards, such as AMD Eyefinity, that don't output DP++ signals.

Superior Materials for Superior Performance Gold-plated HDMI connector and contacts for maximum conductivity and minimum data loss. Special high-grip HDMI plug prevents accidental disconnections. Integral strain relief provides cable and connectors with flexibility and reduces stress.

Specifications

OVERVIEW	
UPC Code	037332200723
Technology	HDMI; DisplayPort
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.9
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Black
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Weight (kg)	0.32
Shipping Weight (lbs.)	0.70
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>