

In most applications where the HDMI cable exceeds 16ft, a signal booster (Model Number: B122-000-60) should be used with this cable to ensure a signal strong enough for your display. An alternate solution is to use a Tripp Lite HDMI over Cat5 Extender (Model Number: B126-1A1) in place of a 50 ft. HDMI cable and signal booster.

High-Speed HDMI Cable, Gripping Connectors (M/M), Black, 50 ft. (15.24 m)

MODEL NUMBER: P568-050-BK-GRP



Securely connect your HDMI-enabled laptop or tablet to a TV, monitor or projector for crystal-clear audio and video.

Features

Tripp Lite's 50-ft. (15.24 m) high-speed HDMI cable securely connects HDMI-enabled laptops, tablets, PCs, Blu-ray players, game consoles or satellite/cable TV boxes to HDTVs, HD monitors, projectors or home theater receivers. The gripping connectors help ensure components stay firmly attached to avoid viewing interruptions.

Enjoy the Clarity of HDMI Video with Multi-Channel Audio Common in home theaters, HDMI allows uncompressed digital video and multi-channel audio signals to travel together in a single cable. This Tripp Lite HDMI cable provides a pure digital connection that supports HD video resolutions up to 1080p, for crystal-clear picture and sound. It is backward compatible with previous HDMI generations, allowing use with lower-resolution HDMI components.

Avoid Signal Disruptions with Extra-Secure Connections Specially designed male connectors firmly grip the HDMI ports on your equipment to help prevent accidental disconnection and signal disruption. With greater port retention than typical HDMI connectors, the gripping connectors resist vibrations that can loosen connections over time. This is especially helpful for ensuring components stay attached in difficult-to-access installations. The gripping connectors are compatible with any full-size HDMI port.

Invest in Quality Construction for Reliable Performance High-quality materials ensure outstanding performance throughout the cable's lifetime. Contacts and connectors are gold-plated to resist corrosion, and double shielding reduces line noise (EMI/RFI) that can disrupt signals traveling through the HDMI cord.

Design a Home Theater to Your Specifications This long HDMI cable allows you greater flexibility in placing your home theater components. For instance, your Blu-ray player or video game system may be hidden away some distance from the connected display.

Lifetime Warranty The P568-050-BK-GRP is backed by Tripp Lite's lifetime limited warranty.

Highlights

- Connects computers, Blu-ray players or game consoles to HDTVs, HD monitors or receivers
- Supports video resolutions up to 1080p for outstanding picture quality
- Firmly grips HDMI ports to prevent accidental disconnects
- 50-ft. (15.24 m) length allows flexibility in home theater set-ups

Applications

- Connect a laptop or tablet to a TV
- Connect a laptop to an A/V connectivity box in a classroom or conference room to present video on a larger screen
- Connect a desktop computer to an HDMI monitor
- Connect a gaming console, like PlayStation (PS3, PS4) or Xbox, to an HDTV
- Connect a Blu-ray disc player to a TV in your home theater
- Use with an Apple digital AV adapter to support iPad2 video mirroring
- Send HD HDMI content to digital signs or point-of-sale displays

Package Includes

- High-Speed HDMI Cable, 50-ft. (15.24 m), with Gripping Connectors - M/M, Black



Specifications

OVERVIEW	
UPC Code	037332210029
Technology	HDMI
INPUT	
Cable Length (ft.)	50
Cable Length (m)	15.24
Cable Length (in.)	600
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Weight (kg)	0.82
Shipping Weight (lbs.)	1.80
ENVIRONMENTAL	
Operating Temperature Range	-10C ~ 80C (14F ~ 176F)
Relative Humidity	0% - 90%, Non-Condensing
Operating Humidity Range	-15C ~ 80C (5F ~ 176F)
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
FEATURES & SPECIFICATIONS	
HDMI Specification	1.3
HDCP Specification	2.2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty