



Powering Business Worldwide

6-ft. AB Parallel Gold Cable (DB25M to Cen36M)

MODEL NUMBER: P606-006-R



Description

Tripp Lite's 6-ft. A-B gold parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Centronics 36 female parallel port. Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing. The cable features gold plated DB25 male/Cent36 male connectors and gold plated copper contacts for superior conductivity. It is manufactured from superior molded cable with integral strain relief and double shielding for maximum EMI/RFI protection. It contains low-capacitance, impedance matched, twisted-pair conductors that protect against cross-talk and other transmission problems. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. Clamshell retail package.

Features

- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing
- Length: 6-ft. Connectors: DB25 male/Cent36 male
- Gold plated connectors and gold plated copper contacts offer superior conductivity
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Specifications

| OVERVIEW | |
|------------|--------------|
| UPC Code | 037332013538 |
| Technology | Parallel |

Highlights

- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing.
- Superior molded cables with integral strain relief and foil-shielding for maximum EMI/RFI protection
- Cables' gold-plated connectors provide superior conductivity and support high-speed bi-directional printing
- Retail packaging

System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with high-speed Bi-Directional communication (although not essential).

Package Includes

- 6-ft. AB Parallel Gold Cable DB25M to Cen36M

| CONNECTIONS | |
|-------------------------------------|---------------------------|
| Side A - Connector 1 | DB25 (MALE) |
| Side B - Connector 1 | CENTRONICS 36 (MALE) |
| PHYSICAL | |
| Color | Black |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Shipping Dimensions (hwd / in.) | 7.50 x 7.25 x 2.25 |
| Shipping Dimensions (hwd / cm) | 19.05 x 18.42 x 5.72 |
| Shipping Weight (lbs.) | 0.84 |
| Shipping Weight (kg) | 0.38 |
| Unit Dimensions (hwd / in.) | 0.000 x 0.000 x 0.000 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.